




















SANS CPA WITHOUT CPA		AVEC CPA WITH CPA		COULEUR COLOR	TOLERANCE POUR DETROMPAGE: ±0.05 KEYING TOLERANCE
REF TE NO	INDICE DE REVISION REVISION NUMBER	REF TE NO	INDICE DE REVISION REVISION NUMBER		
1801178-1	E	1-1801178-1	F	NOIR BLACK	 ECHELLE 3:2
1801178-2	E	1-1801178-2	F	BLEU BLUE	 ECHELLE 3:2
1801178-3	E	1-1801178-3	F	GRIS GREY	 ECHELLE 3:2
1801178-4	E	1-1801178-4	F	JAUNE YELLOW	 ECHELLE 3:2
1801178-5	E	1-1801178-5	F	VERT GREEN	 ECHELLE 3:2
1801178-6	E	1-1801178-6	F	MARRON BROWN	 ECHELLE 3:2
1801178-7	E	1-1801178-7	F	BLANC WHITE	 ECHELLE 3:2
1801178-8	E	1-1801178-8	F	ROUGE RED	 ECHELLE 3:2
1801178-9	E	1-1801178-9	F	ORANGE ORANGE	 ECHELLE 3:2

- NOTES/NOTES:
- 1- 1-1801178-1 REPRESENTE (COD. NOIR) / AS SHOWN (COD. BLACK)
- 2 REPERE ALVEOLES / CAVITY MARKING
- 3 LOGO TE / TE LOGO
- 4 DATE D'ASSEMBLAGE / ASSEMBLY DATE
- 5 CODE DU LIEU D'ASSEMBLAGE / ASSEMBLY LOCATION DATE
- E = EUROPE / EUROPE
- C = CHINE / CHINA
- M = MERCOSUR / MERCOSUR
- H A = AFRICA / AFRIQUE
- 6 NUMERO DE LA MACHINE D'ASSEMBLAGE / NUMBER ASSEMBLY LINE
- 7 REF TE DE L'ASSEMBLAGE (RACINE) / TE ASSEMBLY NO (RACINE)
- 8 REF TE DE L'ASSEMBLAGE (SUFFIXE) / TE ASSEMBLY NO (SUFFIX)
- 9 INDICE DE REVISION PRODUIT / PRODUCT REVISION NUMBER
- 10- PIECES A UTILISER AVEC VOIR TABLEAU "COMPOSANTS ASSOCIES"
/ MATED WITH : SEE TABLE "ASSOCIATED PARTS"



2				1			
LOC	DIST	REVISIONS					
F	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		E		INCREASE IN THE LENGTH OF THE EXTERNAL WALL ABOVE THE LOCKING LATCH	01DEC2009	FJ	XR
		F		MODIFIED CPA TO DECREASE ACTIVATION AND DESACTIVATION FORCE	12JUL2010	FJ	XR
		G		ADDED NUMBER ASSY LINE ON THE PART	21NOV2011	FJ	XR
		H		UPDATED NOTE 5 WITH NEW PLANT CODE	15NOV2018	ASB	XR



SECTION CABLE ADMISSIBLE PAR CONTACT
ACCEPTABLE CABLE SECTIONS PER CONTACT

La section des câbles utilisés doit être comprise entre 0,35 et 2mm² avec un diamètre d'isolant compris entre 1,40mm mini et 2,80mm Maxi.
The cross-section of the cables used must be between 0,35 and 2mm² (with insulator diameter included between 1,40mm mini and 2,80mm Maxi)

CAPOT FIXE 3 VOIES - SORTIE GAUCHE/DROITE FIXED COVER 3 WAYS - LEFT/RIGHT EXIT	POUR GAINÉ ANNELÉE DE 6mm FOR CORRUGATED TUBE OF 6mm	1801467-1
CAPOT FIXE 3 VOIES - SORTIE HAUT/BAS FIXED COVER 3 WAYS - UP/DOWN EXIT	POUR GAINÉ ANNELÉE DE 4.5mm FOR CORRUGATED TUBE OF 4.5mm	1-1801467-1
CAPOT FIXE 3 VOIES - SORTIE AXIALE FIXED COVER 3 WAYS - EXIT IN LINE	POUR GAINÉ ANNELÉE DE 6mm FOR CORRUGATED TUBE OF 6mm	1801168-5
CAPOT ROTATIF 90 DEG. 3 VOIES ROTATIVE COVER 90 DEG. 3 WAYS	POUR GAINÉ ANNELÉE DE 4.5mm FOR CORRUGATED TUBE OF 4.5mm	1-1801168-5
CAPOT (*) COVER	POUR GAINÉ ANNELÉE DE 6mm FOR CORRUGATED TUBE OF 6mm	1801468-1
SUPPORT (*) ADAPTER	POUR GAINÉ ANNELÉE DE 4.5mm FOR CORRUGATED TUBE OF 4.5mm	1-1801468-1
CLIP 1.5 SENSOR II DORE Section 1.4 à 2mm ² RECEPTACLE 1.5 SENSOR II GOLD PLATED Section 1.4 to 2mm ²		1670328-1
CLIP 1.5 SENSOR II DORE Section 0.75 à 1mm ² RECEPTACLE 1.5 SENSOR II GOLD PLATED Section 0.75 to 1mm ²		1670326-1
CLIP 1.5 SENSOR II DORE Section 0.35 à 0.5mm ² RECEPTACLE 1.5 SENSOR II GOLD PLATED Section 0.35 to 0.5mm ²		1564724-1
OBTURATEUR "MINI-ETANCHE" "MINI-ETANCHE" PLUGGING PIN		
PORTE-LANGUETTES 3 VOIES HP 3 WAYS TAB CONNECTOR HP		1801177-X
DESCRIPTION TITLE	TE NO REF TE	
COMPOSANTS ASSOCIES ASSOCIATED PARTS		

(*) : POUR LE CAPOT ROTATIF, PRENDRE : SUPPORT + CAPOT FOR THE ROTATIVE COVER, TAKE: ADAPTER + COVER		
ORANGE ORANGE	PBT-GF15 (MATIERE: HB) (HB MATERIAL)	CPA CPA
VERT GREEN	SILICONE LUBRIFIE A 5% ; DURETE 30 SHORE A LUBRICATED SILICON TO 5% ; HARNESS 30 SH. A	JOINT GROMMET GROMMET SEAL
NOIR BLACK	PBT-GF15 (MATIERE: HB) (HB MATERIAL)	GRILLE ARRIERE REAR GRID
VERT GREEN	SILICONE LUBRIFIE A 4% ; DURETE 50 SHORE A LUBRICATED SILICON TO 4% ; HARNESS 50 SH. A	JOINT INTERFACIAL INTERFACE SEAL
VOIR TABLEAU DES REF. SEE TABLE OF PART NO	PBT-GF15 (MATIERE: HB) (HB MATERIAL)	DOUBLE VERROUILLAGE CODAGE (VOIR TABLEAU DES REFS) SECONDARY LOCKING CODING (SEE TABLE OF PART NO)
NOIR BLACK	PBT-GF15 (MATIERE: HB) (HB MATERIAL)	BOITIER PORTE-CLIPS RECEPTACLE HOUSING
COULEUR COLOR	MATIERE MATERIAL	DESCRIPTION TITLE
		REP. ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. BARLEMON CHK J. DAHER	23NOV2007	TE Connectivity	
DIMENSIONS: mm		APVD J. DAHER	23NOV2007	NAME 3 WAYS RECEPTACLE CONNECTOR HP PORTE-CLIPS 3 VOIES HP	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-15378		SIZE -	
0 PLC ± 1 PLC ±0.2 2 PLC ± 3 PLC ± 4 PLC ±		APPLICATION SPEC 411-15712		CAGE CODE -	
ANGLES ±2°		FINISH SEE TABLE VOIR TABLEAU		DRAWING NO A100779	
MATERIAL SEE TABLE VOIR TABLEAU		WEIGHT 7.1g / 1.4g with CPA		RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 3:1	
				SHEET 1 OF 1	
				REV H	