

A.  
System  
Overview

B1.  
Cable Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index



## HSTTV Heat Shrink 4 Foot Pieces

- Applications include insulating and protecting wires and cables
- Fast shrink time
- Voltage: 600 V
- Shrink ratio: 2:1
- Flammability: Meets UL 224 VW-1
- UL Recognized, CSA Certified
- Mil Spec: AMS-DTL-23053/5 Class 3
- Temperature range: -67°F to 275°F (-55°C to 135°C)
- For dry locations
- Material: Black cross-linked Polyolefin



| Part Number    | Nominal Diameter |      | Min. Expanded I.D. |      | Max. Recovered I.D. |      | Nominal Recovered Wall Thickness |     | Std. Pkg. Qty. | Std. Ctn. Qty. |
|----------------|------------------|------|--------------------|------|---------------------|------|----------------------------------|-----|----------------|----------------|
|                | In.              | mm   | In.                | mm   | In.                 | mm   | In.                              | mm  |                |                |
| HSTTV05-48-Q   | 0.046            | 1.2  | 0.046              | 1.2  | 0.023               | 0.6  | 0.016                            | 0.4 | 25             | —              |
| HSTTV05-48-TL  | 0.046            | 1.2  | 0.046              | 1.2  | 0.023               | 0.6  | 0.016                            | 0.4 | 250            | —              |
| HSTTV06-48-Q   | 0.063            | 1.6  | 0.063              | 1.6  | 0.031               | 0.8  | 0.017                            | 0.4 | 25             | —              |
| HSTTV06-48-TL  | 0.063            | 1.6  | 0.063              | 1.6  | 0.031               | 0.8  | 0.017                            | 0.4 | 250            | —              |
| HSTTV09-48-Q   | 0.093            | 2.4  | 0.093              | 2.4  | 0.046               | 1.2  | 0.020                            | 0.5 | 25             | —              |
| HSTTV09-48-TL  | 0.093            | 2.4  | 0.093              | 2.4  | 0.046               | 1.2  | 0.020                            | 0.5 | 250            | —              |
| HSTTV12-48-Q   | 0.125            | 3.2  | 0.125              | 3.2  | 0.062               | 1.6  | 0.020                            | 0.5 | 25             | —              |
| HSTTV12-48-TL  | 0.125            | 3.2  | 0.125              | 3.2  | 0.062               | 1.6  | 0.020                            | 0.5 | 250            | —              |
| HSTTV19-48-Q   | 0.187            | 4.8  | 0.187              | 4.8  | 0.093               | 2.4  | 0.020                            | 0.5 | 25             | —              |
| HSTTV19-48-TL  | 0.187            | 4.8  | 0.187              | 4.8  | 0.093               | 2.4  | 0.020                            | 0.5 | 250            | —              |
| HSTTV25-48-Q   | 0.250            | 6.4  | 0.250              | 6.4  | 0.125               | 3.2  | 0.025                            | 0.6 | 25             | —              |
| HSTTV25-48-TL  | 0.250            | 6.4  | 0.250              | 6.4  | 0.125               | 3.2  | 0.025                            | 0.6 | 250            | —              |
| HSTTV38-48-Q   | 0.375            | 9.5  | 0.375              | 9.5  | 0.187               | 4.8  | 0.025                            | 0.6 | 25             | —              |
| HSTTV38-48-TL  | 0.375            | 9.5  | 0.375              | 9.5  | 0.187               | 4.8  | 0.025                            | 0.6 | 250            | —              |
| HSTTV50-48-Q   | 0.500            | 12.7 | 0.500              | 12.7 | 0.250               | 6.4  | 0.025                            | 0.6 | 25             | —              |
| HSTTV50-48-T   | 0.500            | 12.7 | 0.500              | 12.7 | 0.250               | 6.4  | 0.025                            | 0.6 | 200            | —              |
| HSTTV75-48-5   | 0.750            | 19.1 | 0.750              | 19.1 | 0.375               | 9.5  | 0.030                            | 0.8 | 5              | —              |
| HSTTV75-48-CQ  | 0.750            | 19.1 | 0.750              | 19.1 | 0.375               | 9.5  | 0.030                            | 0.8 | 125            | —              |
| HSTTV100-48-5  | 1.00             | 25.4 | 1.00               | 25.4 | 0.500               | 12.7 | 0.035                            | 0.9 | 5              | —              |
| HSTTV100-48-LQ | 1.00             | 25.4 | 1.00               | 25.4 | 0.500               | 12.7 | 0.035                            | 0.9 | 75             | —              |
| HSTTV150-48-5  | 1.50             | 38.1 | 1.50               | 38.1 | 0.750               | 19.1 | 0.040                            | 1.0 | 5              | —              |

Order number of pieces required, in multiples of Standard Package Quantity.