

19

SOCKET 1/2" hexagon UD profile


- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- GEDORE vanadium steel 31CrV3, polished, chrome-plated
- * not standardised

12.5

1/2"



mm



Code	No.	W	*	mm	L	d ₁	d ₂	t	W	W	£
6130020	19 8			8	38.0	13.0	22.5	15.0	55	10	
6130100	19 9		*	9	38.0	14.2	22.5	15.0	56	10	
6130290	19 10			10	38.0	15.5	22.5	13.5	56	10	
6130370	19 11			11	38.0	16.7	22.5	12.5	58	10	
6130450	19 12			12	38.0	18.0	22.5	12.5	58	10	
6130530	19 13			13	38.0	19.2	22.5	12.5	61	10	

Code	No.	W	*	mm	L	d ₁	d ₂	t	W	W	£
6130610	19 14			14	38.0	20.5	22.5	12.5	63	10	
6130880	19 15			15	39.5	21.7	23.8	15.0	74	10	
6130960	19 16			16	39.5	22.5	23.8	15.0	75	10	
6131180	19 17			17	39.5	24.0	22.5	15.0	74	10	
6131260	19 18			18	39.5	25.5	23.0	17.0	73	10	
6131340	19 19			19	40.0	26.7	24.2	17.0	85	10	
6131420	19 20			20	40.0	28.0	25.5	17.0	96	10	
6131500	19 21			21	41.5	29.2	26.0	18.5	106	10	
6131690	19 22			22	41.5	30.5	26.3	18.5	112	10	
6131770	19 23		*	23	41.5	31.7	27.5	18.5	122	10	
6131850	19 24			24	41.5	33.0	28.0	18.5	132	10	
6131930	19 25		*	25	41.5	34.2	28.8	18.5	139	10	
6132070	19 26		*	26	41.5	35.5	29.4	18.5	148	10	
6132150	19 27			27	41.5	36.7	30.0	18.5	157	10	
6132230	19 28		*	28	43.0	38.0	30.5	20.0	168	10	
6132310	19 29		*	29	43.0	39.2	31.2	20.0	181	10	
6132580	19 30			30	43.0	40.5	32.5	20.5	193	10	
6132740	19 32			32	44.5	43.0	34.5	22.5	226	10	
2545306	19 33		*	33	44.5	44.2	36.0	22.5	226	10	
6138270	19 34			34	44.5	45.5	37.0	22.5	259	10	
1718711	19 36		*	36	44.5	48.0	38.0	22.5	271	10	

D 19

SOCKET 1/2" bi-hexagon UD profile


- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- GEDORE vanadium steel 31CrV3, polished, chrome-plated
- * not standardised

12.5

1/2"



mm



Code	No.	W	*	mm	L	d ₁	d ₂	t	W	W	£
6133040	D 19 8			8	38.0	13.0	22.5	7.0	51	10	
6133120	D 19 9		*	9	38.0	14.2	22.5	8.0	52	10	
6133200	D 19 10			10	38.0	15.5	22.5	13.5	56	10	
6133390	D 19 11			11	38.0	16.7	22.5	12.5	57	10	
6133470	D 19 12			12	38.0	18.0	22.5	12.5	57	10	
6133550	D 19 13			13	38.0	19.2	22.5	12.5	59	10	
6133630	D 19 14			14	38.0	20.5	22.5	12.5	61	10	
6133710	D 19 15			15	39.5	21.7	23.8	15.0	72	10	
6133980	D 19 16			16	39.5	22.5	23.8	15.0	72	10	
6134010	D 19 17			17	39.5	24.0	22.5	15.0	70	10	
6134280	D 19 18			18	39.5	25.5	23.0	17.0	68	10	
6134360	D 19 19			19	40.0	26.7	24.2	17.0	81	10	
6134440	D 19 20			20	40.0	28.0	25.5	17.0	90	10	
6134520	D 19 21			21	41.5	29.2	26.0	18.5	101	10	
6134600	D 19 22			22	41.5	30.5	26.3	18.5	106	10	
6134790	D 19 23		*	23	41.5	31.7	27.5	18.5	118	10	
6134870	D 19 24			24	41.5	33.0	28.0	18.5	123	10	
6134950	D 19 25		*	25	41.5	34.2	28.8	18.5	131	10	
6135090	D 19 26		*	26	41.5	35.5	29.4	18.5	139	10	
6135170	D 19 27			27	41.5	36.7	30.0	18.5	143	10	
6135250	D 19 28		*	28	43.0	38.0	30.5	20.0	163	10	
6135330	D 19 29		*	29	43.0	39.2	31.2	20.0	168	10	
6135410	D 19 30			30	43.0	40.5	32.5	20.5	182	10	
6135760	D 19 32			32	44.5	43.0	34.5	22.5	204	10	
6135840	D 19 33		*	33	44.5	44.2	36.0	22.5	221	10	
2545314	D 19 34		*	34	44.5	45.5	37.0	22.5	251	10	
2194686	D 19 36		*	36	44.5	48.0	38.0	22.5	271	10	

"AF

Code	No.	W	AF	L	d ₁	d ₂	t	W	W	£
6136060	D 19 5/16AF		5/16	38.0	13.0	22.5	7.0	52	5	
6136140	D 19 11/32AF		11/32	38.0	13.9	22.5	8.0	54	5	
6136220	D 19 3/8AF		3/8	38.0	14.9	22.5	15.0	55	5	
6136300	D 19 13/32AF		13/32	38.0	15.9	22.5	13.5	55	5	
6136490	D 19 7/16AF		7/16	38.0	16.7	22.5	12.5	56	5	
6136570	D 19 1/2AF		1/2	38.0	18.7	22.5	12.5	58	5	
6136650	D 19 9/16AF		9/16	38.0	20.7	22.5	12.5	61	5	
6136730	D 19 19/32AF		19/32	39.5	21.7	23.8	15.0	70	5	
6136810	D 19 5/8AF		5/8	39.5	22.5	23.8	15.0	73	5	
6137030	D 19 11/16AF		11/16	39.5	24.7	22.5	17.0	66	5	
6137110	D 19 3/4AF		3/4	40.0	26.7	24.2	17.0	84	5	
6137380	D 19 25/32AF		25/32	40.0	27.7	25.3	17.0	90	5	
6137460	D 19 13/16AF		13/16	41.5	28.5	25.7	18.5	97	5	
6137540	D 19 7/8AF		7/8	41.5	30.6	26.5	18.5	105	5	
6137620	D 19 15/16AF		15/16	41.5	32.6	28.3	18.5	126	5	
6137700	D 19 1AF		1	41.5	34.6	28.9	18.5	138	5	
6137890	D 19 1.1/16AF		1.1/16	41.5	36.7	30.0	18.5	147	5	
6137970	D 19 1.1/8AF		1.1/8	43.0	38.6	31.0	20.0	159	5	
6138000	D 19 1.3/16AF		1.3/16	43.0	40.6	32.5	20.5	183	5	
6138190	D 19 1.1/4AF		1.1/4	44.5	42.6	34.5	22.5	207	10	

Whitw.

Code	No.		L	d ₁	d ₂	t			£
6138780	D 19 3/16W		3/16	38.0	17.0	22.5	12.5	54	10
6138860	D 19 1/4W		1/4	38.0	19.5	22.5	12.5	57	10
6138940	D 19 5/16W		5/16	39.5	21.9	23.8	15.0	69	10
6139080	D 19 3/8W		3/8	39.5	25.5	23.0	17.0	66	10
6139160	D 19 7/16W		7/16	41.5	28.8	26.0	18.5	96	10
6139240	D 19 1/2W		1/2	41.5	32.1	27.8	18.5	124	10
6139320	D 19 9/16W		9/16	41.5	34.9	29.2	18.5	137	10
6139400	D 19 5/8W		5/8	43.0	37.8	30.5	20.0	166	10
6139590	D 19 11/16W		11/16	43.0	41.0	33.0	20.5	184	10
6138430	D 19 3/4W		3/4	44.5	44.2	36.0	22.5	225	10