

3M

Duct Tape

3939

Technical Data

June, 2005

Product Description 3M™ Duct Tape 3939 is composed of waterproof polyethylene film over cloth scrim backing with a rubber adhesive used for demanding duct tape applications.

Product Construction	Backing	Adhesive	Colors	Standard Roll Length	Standard Roll Width
	Polyethylene film over cloth scrim	Rubber	Silver	60 yds. (54.8 m)	0.94, 1.89, 2.83, 3.78 in. (24, 48, 72, 96 mm)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

ASTM Test Method		
Adhesion to Steel:	55 oz./in. width (60 N/100 mm)	D-3330
Tensile Strength:	25 lbs./in. width (438 N/100 mm)	D-3759
Elongation at Break:	17%	D-3759
Thickness:	9.0 mils (0.23 mm)	D-3652
Temperature Use Range:	Up to 200°F (93°C)	
Flammability:	Meets UL 723 (Flame spread 0, Smoke developed 30)	E-84

Features

- Offers easy tear and conformability.
- Meets UL 723, HUD, and BOCA codes.
- Low tack roll edges (48 mm) so edges stay cleaner for less surface contamination and less waste.
- Individual roll wrap (48 mm) that preserves integrity of the roll for less waste.
- Product number printed in core to insure that correct product is used.
- Polyethylene coated cloth scrim that resists moisture to prolong tape bond.
- Good tensile strength for tough applications.
- Rubber adhesive that adheres aggressively to most surfaces for good holding power and a tight seal.

3M™ Duct Tape

3939

Application Ideas

- Hanging polyethylene drapes for containment activities, industrial masking and sandblast overspray protection.
- Patching, reinforcing, bundling, moisture proofing, sealing, splicing, temporary repair.
- Taping and splicing insulation.
- Useful in the convention industry for holding and seaming carpet padding, taping down cords and hinging poster board panels.

Storage

Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% R.H. in the original carton.

Shelf Life

To obtain best performance, use this product within one year from date of manufacture.

Product Use

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy

Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability

Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Business Industrial Adhesives and Tapes Division

3M Center, Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

Printed in U.S.A.
©3M 2005 70-0709-5181-2 (6/05)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[3939-24mmx55m](#) [3939-72mmx55m](#) [3939-96mmx54.8m](#) [3939](#)