

# J Journeyman™ Series

The Journeyman™ line of hand tools represents the best of Klein quality and workmanship combined with the latest innovations in handle design.

J Journeyman™ Series




F o r  
P r o f e s s i o n a l s . . . . .  
s i n c e 1857®





## Side-Cutting Pliers

### Features:



**JOURNEYMAN**

## High-Leverage Side-Cutting Pliers

**JOURNEYMAN**

#### Additional Features:

- *High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.*
- *Streamlined design with sure-gripping, cross-hatched knurled jaws.*
- *Induction-hardened cutting knives for long life.*
- *Hot-riveted joint ensures smooth action and no handle wobble.*



J2000-9NE

#### 2000 Series\* – Heavy-duty cutting knives

J2000-9NE	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.13
-----------	-------------	-----------------	------------------	----------------	--------------	----------------	------------	------------------	------

\*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

## High-Leverage Side-Cutting Pliers – Fish-Tape Pulling

**JOURNEYMAN**

#### Additional Features:

- *Quickly and easily pulls 1/8" or 1/4" flat steel fish tape without damaging the tape.*
- *High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.*
- *Streamlined design with sure-gripping, cross-hatched knurled jaws.*
- *Induction-hardened cutting knives for long life.*
- *Hot-riveted joint ensures smooth action and no handle wobble.*



J2000-9NETP

#### 2000 Series\* – Heavy-duty cutting knives

J2000-9NETP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	dark blue/black	1.11
-------------	-------------	-----------------	------------------	----------------	--------------	----------------	------------	-----------------	------

\*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

## High-Leverage Side-Cutting Pliers – Connector Crimping

JOURNEYMAN™

### Additional Features:

- Crimping die behind hinge for superior leverage crimping non-insulated connectors, lugs and terminals.
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Streamlined design with rounded nose and sure-gripping, cross-hatched knurled jaws.
- Induction-hardened cutting knives for long life.
- Hot-riveted joint ensures smooth action and no handle wobble.



J213-9NECR

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
J213-9NECR	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	yellow/black	1.13
<b>2000 Series* – Heavy-duty cutting knives</b>									
J2000-9NECR*	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.12

\*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

## High-Leverage Side-Cutting Pliers – Connector Crimping & Fish Tape Pulling

JOURNEYMAN™

### Additional Features:

- Built-in crimper works on non-insulated connectors, lugs, and terminals.
- Built-in channel pulls steel fish tape without damaging the tape.
- 2000 series heavy-duty cutting knives cut ACSR, screws, nails, and most hardened wire.



J2000-9NECRTP

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
J2000-9NECRTP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.13

\*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

## 8" Universal Combination Pliers

JOURNEYMAN™

### Additional Features:

- Universal tapered head-design allows greater access in confined spaces.
- Precision machined pipe-grip for greater gripping power.
- Crimping die behind hinge for superior leverage crimping of non-insulated connectors, lugs and terminals.



J12098

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
J12098	Universal	8-3/4" (222 mm)	1-25/32" (45 mm)	1-1/32" (26 mm)	17/32" (13 mm)	3/4" (19 mm)	Journeyman	dark blue/black	.82

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.





## Side-Cutting Pliers

### 8" High-Leverage Side-Cutting Pliers

JOURNEYMAN™

#### Additional Features:

- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power.
- 2000 series cut screws, nails, and most hardened wire.
- Combination polished and black-oxide finishes.



J2000-8

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
J2000-8	New England Tapered	8-13/16" (224 mm)	1-7/16" (37 mm)	1-7/64" (28 mm)	5/8" (16 mm)	3/4" (19 mm)	Journeyman	light blue/black	.93

### 7" Side-Cutting Pliers

JOURNEYMAN™

#### Additional Features:

- 2000 series cut screws, nails, and most hardened wire.
- Combination polished and black-oxide finishes.



J2001-7NE

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
J2001-7NE	New England	7-9/16" (192 mm)	1-9/32" (33 mm)	1-1/16" (27 mm)	1/2" (13 mm)	5/8" (16 mm)	Journeyman	light blue/black	.61

## Diagonal-Cutting Pliers

### High-Leverage Diagonal-Cutting Pliers

JOURNEYMAN™

#### Additional Features:

- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting and gripping power than other plier designs.
- Short jaws and beveled cutting edges permit close cutting of wire.
- Induction-hardened cutting knives for long life.
- Hot-riveted joint ensures smooth action and no handle wobble.



J2000-28

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Handle Finish	Handle Color	Weight (lbs.)
J228-8	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	red/black	.67
<b>2000 Series* – Heavy-duty cutting knives</b>								
J2000-28	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	light blue/black	.67

\*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

## High-Leverage Diagonal-Cutting Pliers – Angled Head

JOURNEYMAN™



J2000-48

### Additional Features:

- Angled head design for easy work in confined spaces.
- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting and gripping power than other plier designs.
- Short jaws and beveled cutting edges permit close cutting of wire.
- Induction-hardened cutting knives for long life.
- Hot-riveted joint ensures smooth action and no handle wobble.

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Handle Finish	Handle Color	Weight (lbs.)
J248-8	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	red/black	.61
<b>2000 Series* – Heavy-duty cutting knives</b>								
J2000-48	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	light blue/black	.61

\*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

## Long-Nose Pliers

### Heavy-Duty Long-Nose Pliers – Side-Cutting

JOURNEYMAN™



J203-8

### Additional Features:

- Induction-hardened, long-lasting cutting knives.
- Heavier design for greater cutting power.
- Extended handles provide added reach and leverage.
- Slim head design for working in confined areas.
- Hot-riveted joint ensures smooth action and no handle wobble.

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
J203-8	8-9/16" (218 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)	Journeyman	yellow/black	.63
<b>Wire Stripping – Cleanly strips 12 AWG wire</b>									
J203-8N	8-9/16" (218 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)	Journeyman	yellow/black	.64

### Standard Long-Nose Pliers

JOURNEYMAN™



J203-7

### Additional Features:

- Slim head design for working in confined areas.
- Induction-hardened, long-lasting cutting knives.
- Knurled jaws for sure wrapping and looping.
- Hot-riveted joint ensures smooth action and no handle wobble.

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
J203-6	6-3/4" (171 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	Journeyman	yellow/black	.30
J203-7	7-5/16" (186 mm)	2-7/16" (62 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	Journeyman	yellow/black	.33

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.





## Pump Pliers

### Pump Pliers

JOURNEYMAN™

#### Additional Features:

- Secure tongue and groove design for non-slip grip – even with heavy pressure.
- Wide range of versatile jaw positions.
- Tension-loaded joint to reduce handle wobble for sure gripping.
- Induction-hardened jaws for long life.



J502-10

Cat. No.	Overall Length	Max. Jaw Capacity	Handle Finish	Handle Color	Weight (lbs.)
J502-10	10-1/4" (260 mm)	1-3/4" (45 mm)	Journeyman	yellow/black	1.02

## Crimping Tool

### Crimping/Cutting Tool – Non-Insulated/Insulated Connectors

JOURNEYMAN™

#### Additional Features:

- Designed to crimp insulated and non-insulated 10 to 22 AWG solderless terminals and connectors.
- Tapered nose design for working in confined spaces.
- Contoured thumb area for additional comfort and positive feel.
- Specially hardened cutter.
- Hot-riveted joint ensures smooth action and no handle wobble.



J1005

Cat. No.	Overall Length	Handle Finish	Handle Color	Weight (lbs.)
J1005	9-3/4" (248 mm)	Journeyman	red/black	.84

## Cable Cutter

### High-Leverage Cable Cutter

JOURNEYMAN™

#### Additional Features:

- Cuts up to 4/0 aluminum AWG (no ACSR), 2/0 AWG soft copper and 100-pair 24 AWG communications cable.
- High-leverage for greater cutting power.
- Precision, one-hand shearing action.



J63050

Cat. No.	Overall Length	Handle Finish	Handle Color	Weight (lbs.)
J63050	9-9/16" (243 mm)	Journeyman	red/black	.98

**WARNING:** Do NOT use to cut steel or ACSR.

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.