

Single-Pole Fuse Blocks

Specifications

Description: Single-pole fuse block for ¼" x 1¼" (6.4 x 31.8mm) size fuses.

Dimensions: See Dimensions illustrations.

Construction: Bakelite base width ½" (12.7mm); spring-bronze, bright tin-lead plate clips.

Ratings:


Volts: — 250V

Amps: — 30A



4405 - 0° Solder terminals with integral terminal and clip

Dimensions - in (mm)




4406 - Side solder terminal



4574 - Spare fuse block

Dimensions - in (mm)




2499 - Side quick-connect

Agency Information: UL

Recognized, Guide IZLT2, File E14853

Terminals: ¼" (6.4mm); 15A, 250V

Dimensions - in (mm)



Note: Mounting screw hole diameter is 0.147" (3.7mm). Counterbore diameter, 0.636" (8.0mm). Max Mounting Screw No. 6.