



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PS2408

8-outlet Vertical Power Strip with 15-ft. Cord

Highlights

- 8 outlets
- Convenient and safe covered, on/off switch
- 15-amp circuit breaker
- 15 ft. cord
- 24" length



Description

Tripp Lite's PS2408 power strip offers 15 amp, 120v multi-outlet AC power distribution in a convenient 24 inch mountable housing. Offers horizontal or vertical power distribution in rackmount, raceway and workbench applications. Includes 8 NEMA 5-15R output receptacles with 2.48 inch center-to-center spacing, 15 ft AC line cord and lighted power switch with locking transparent cover to prevent accidental shutoff. Sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory or factory environments.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 8 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: 24 in. corded, mountable power strip

Applications

- Offers vertical or horizontal multi-outlet power distribution in rack enclosures, raceways, desktops and more.

Package Includes

- PS2408
- Mounting hardware
- Instruction manual

Features

- Sturdy all-metal 24 inch corded strip format with 2.48 inch center-to-center outlet spacing
- Included mounting hardware supports vertical or horizontal mounting in rack enclosures, raceways and more
- Includes 8 NEMA 5-15R output receptacles
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- Lighted power switch with locking transparent cover prevents accidental shutoff
- 15 amp electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	8 Nema 5-15R
Outlet spacing	2.48 in.
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	Nema 5-15P
Input plug features	Black
Input cord length (ft.)	15
Input cord length (m)	4.572
Input cord gauge, type	14/3 SJT
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Lighted 2 position switch controls power to all outlets
Locking switch cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Unit Dimensions (HWD/in)	24 x 1.5 x 1.5
Unit Dimensions (HWD/cm)	61 x 3.8 x 3.8
Unit weight (lbs)	3.2
Unit weight (kg)	1.4528
Material of construction	Aluminum
Mounting accessories included	Includes mounting clips
Receptacle Color	Black
AC line cord color	Black
Style	Bench/Cabinet Mount
Form factors supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Outlets center to center measurement	63mm
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363

cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=192.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.