

GNM1M2R61A473MA01#

" # " indicates a package specification code.

To be discontinued

General


85℃

Reflow OK

RoHS

< List of part numbers with package codes >
GNM1M2R61A473MA01D

Shape



L size	1.37 ± 0.15mm
W size	1.0 ± 0.15mm
T size	0.6 ± 0.1mm
Distance between external terminals P	0.64 ± 0.05mm
Size code in inch(mm)	0504 (1410)

References

Packaging	Specifications	Minimum quantity
D	φ 180mm Paper taping	4000

Mass (typ.)	
1 piece	4.7mg
φ 180mm Reel	137g

Specifications

Capacitance	47000pF ± 20%
Rated voltage	10Vdc
Temperature characteristics (complied standard)	X5R(EIA)
Capacitance change rate	± 15.0%
Temperature range of temperature characteristics	-55 to 85
Operating temperature range	-55 to 85

⚠ Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.