

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0395066702](#)  
**Status:** **Obsolete**  
**Description:** 3.50mm (.138") Pitch Eurostyle™ Horizontal PCB Header, with Threaded Retention Inserts and Reverse Imprinting, Green Housing, Gold (Au) Plated, 2 Circuits

**Documents:**  
[Drawing \(PDF\)](#)

**General**

|                |                           |
|----------------|---------------------------|
| Product Family | Terminal Blocks           |
| Series         | <a href="#">39506</a>     |
| Application    | Wire-to-Board             |
| Comments       | with Reverse Imprinting   |
| Component Type | PCB Header                |
| Product Name   | ESE, Eurostyle™ Pluggable |
| Type           | Euro Block                |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Circuits (Loaded)             | 2               |
| Entry Angle                   | N/A             |
| Lock to Mating Part           | Yes             |
| Number of Rows                | 1               |
| Orientation                   | Horizontal      |
| PC Tail Length                | 3.50mm (.138")  |
| PCB Thickness - Recommended   | 2.50mm (.098")  |
| Panel Mount                   | No              |
| Pitch - Mating Interface      | 3.50mm (.138")  |
| Pitch - Termination Interface | 3.50mm (.138")  |
| Polarized to Mating Part      | Yes             |
| Shrouded                      | Fully           |
| Stackable                     | No              |
| Temperature Range - Operating | -40°C to +105°C |
| Wire Size AWG                 | N/A             |


**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 8A   |
| Voltage - Maximum             | 300V |

**Material Info**

**Reference - Drawing Numbers**

|                       |                            |
|-----------------------|----------------------------|
| Product Specification | PS-39500-001               |
| Sales Drawing         | SD-39501-002, SD-39506-001 |



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed  
**Low-Halogen Status  
Not Reviewed**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

**Search Parts in this Series**

[39506Series](#)

**Mates With**

Most 3.50mm (.138") Pitch Industry  
Standard Plugs, [39504](#) Horizontal Plug with  
Retention Screws, [39507](#) Vertical Plug with  
Retention Screws