




Nickel-Plated Long Arm Hex L-keys

Nickel-Plated



352 Metric L-wrench Hex Key, Long Arm high alloy CVM steel, hardened, nickel plated. Precision machined, burr free chamfered ends.


Item No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
352 01	1.5	89	3.5	14	.6	.01	10
352 02	2.0	99	3.9	16	.6	.01	10
352 04	2.5	110	4.3	18	.7	.02	10
352 06	3.0	124	4.9	20	.8	.02	10
352 08	4.0	138	5.4	25	1.0	.04	10
352 10	5.0	158	6.2	28	1.1	.07	10
352 11	6.0	178	7.0	32	1.3	.12	10
352 12	7.0	187	7.4	34	1.3	.17	10
352 14	8.0	196	7.7	36	1.4	.23	10
352 17	10.0	219	8.6	40	1.6	.40	10
352 19	12.0	245	9.6	45	1.8	.77	1
352 21	14.0	277	10.9	56	2.2	1.12	1
352 23	17.0	316	12.4	63	2.5	1.80	1
352 27	19.0	355	14.0	70	2.8	2.46	1



352 97 Metric Hex L-wrench Set 9 Pc. in Plastic Holder
Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

Item No.	lbs.	pkg.
352 97	1.00	1

Nickel-Plated



352 Inch L-wrench Hex Key, Long Arm

Item No.	Inch	mm	Inch	lbs.	pkg.
352 31	.050	75	3.0	.01	10
352 33	1/16	78	3.1	.01	10
352 35	5/64	82	3.2	.01	10
352 37	3/32	85	3.3	.01	10
352 39	7/64	92	3.6	.01	10
352 41	1/8	95	3.7	.02	10
352 43	9/64	100	3.9	.03	10
352 51	5/32	105	4.1	.03	10
352 52	3/16	113	4.4	.05	10
352 53	7/32	122	4.8	.07	10
352 54	1/4	135	5.3	.10	10
352 55	5/16	152	6.0	.18	10
352 56	3/8	173	6.8	.30	10
352 57	1/2	209	8.2	.77	1
352 58	9/16	230	9.1	1.04	1
352 59	5/8	245	9.6	1.27	1
352 61	3/4	286	11.3	2.01	1



352 95 Inch Hex L-wrench Set 13 Pc. in Plastic Holder

Equipped with .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Item No.	lbs.	pkg.
352 95	1.02	1