



PANEL THICKNESS	X dimension
0.75-1.25 [.030-.049]	19.2- <i>a1</i> [.7561]
1.25-2.0 [.049-.079]	19.4- <i>a1</i> [.7641]
2.0-3.0 [.079-.118]	19.8- <i>a1</i> [.7801]




SWITCH FUNCTION	
PDS. 1	PDS. 2
OFF	<DN>
OPEN	1-1A



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.XX=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 15A @ 125VAC OR
6A @ 250VAC
5. MATERIALS: TERMINALS: Silver Plated Copper Alloy
CONTACTS: Coin Silver, Silver Plated
6. ELECTRIC LIFE: 10,000 cycles
7. CONTACT RESISTANCE: <20 Mega Ω
8. INSULATION RESISTANCE: >1000 Mega Ω
9. DIELECTRIC STRENGTH: >1500 V 1 minute
>3000 V between poles
10. 2002/95/EC (ROHS) COMPLAINT



REVISION HISTORY			
REV.	ECN No.	DESCRIPTION	DATE
B	17020	UPDATE NOTES, FIXED POSITION	2/22/07
A	13135	RELEASED FOR PRODUCTION	5/13/03
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
TITLE			
R1966FBLKBLKAG			
SCALE	DATE	DR	DWG
1.5:1	2/22/07	TN	M304197
REV			
B			