

SPECIFICATIONS


(RoHS Compliant)

Model Number: BD24B3
Part Number: 19030621A

Drawing Number: 26021647A02
Jan.25.2013



Mechanical Drawing:



Motor:

Nominal Voltage	= 24 vdc
Operating Voltage Range	= 12 - 28 vdc
Nominal Running Current	= 0.48 amps
Locked Rotor Current	= 0.95 amps
Running Power	= 11.5 watts
Average Speed	= 3100 rpm
Bearings	= Ball
Air Flow	= 26 cfm
Acoustic	= 51.2 dBA

Construction:

Venturi: Plastic, Black, UL 94V-0
Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 78,000 hours at 40°C.

Additional Features:

Brushless DC Motor	
Polarity Protected	
Locked Rotor Protection	
Automatic Restart Capability	
Operating Temperature:	-10°C to 70°C
Storage Temperature:	-40°C to 85°C

Termination:

12" Lead wires, AWG 22, UL 1061

Red = Power (+)
Black = Ground (-)

Agency Certifications:

UL, CE