




D


C

B

A



- 1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC, COLOR NATURAL.
PIN CONTACTS: PHOSPHOR BRONZE.
GROUND BUSSES: PHOSPHOR BRONZE.
- 2 CONTACTS & GROUND BUSES: 0.00076(.000030) MIN. GOLD PER ASTM B 488 ON CONTACT AREA,
0.00254-0.00762(.000100-.000300) MATTE TIN PER ASTM B 545 ON SOLDER TAIL, ALL OVER 0.00127-0.00254(.000050-.000100) MATTE NICKEL PER SAE AMS-QQ-N-290 ON ENTIRE CONTACT.
- 3 DATE CODE MARKED IN AREA INDICATED.



RECOMMENDED PC BOARD HOLE LAYOUT
(VIEWED FROM CONNECTOR SIDE)
SCALE 5:1

OBSOLETE	74.93[2.950]	59	77.42[3.048]	79.88[3.145]	81.64[3.214]	120	5536273-5
	62.23[2.450]	49	64.72[2.548]	67.18[2.645]	68.94[2.714]	100	5536273-4
	24.13[.950]	19	26.62[1.048]	29.08[1.145]	30.84[1.214]	40	5536273-1
	E	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ CHK D. DIXON APP'D D. DIXON	01-20-05 01-20-05 01-20-05	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-1272		NAME PLUG ASSEMBLY, 10.92[.430] STACK, 4.7[.185] TAIL, BOARD TO BOARD, MICRO-STRIP	
	0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± 0.13 [.005] 4. PLC ± - ANGLES ± -	APPLICATION SPEC 114-11005		SIZE A1	
MATERIAL	FINISH	WEIGHT		RESTRICTED TO	
1	2	CUSTOMER DRAWING		SCALE 10:1 SHEET 1 OF 1 REV 02	