


147 Central Avenue  
Hackensack, New Jersey 07601  
Tel: 201-489-8989 • Fax: 201-489-6911



**CHICAGO MINIATURE LAMP, INC.**  
WHERE INNOVATION COMES TO LIGHT

## T-3 1/4 Wedge Base



| Part Number | Design Voltage | Amps | MSCP | Life Hours | Filament Type |
|-------------|----------------|------|------|------------|---------------|
| CM559       | 1.38           | .56  | .33  | 50         | S-2           |
| CM127       | 2.47           | .25  | .45  | 30         | C-2R          |
| CM285       | 5.00           | .09  | .25  | 1,500      | C-2R          |
| CM740       | 5.00           | .07  | .19  | 1,500      | C-6           |
| CM820       | 6.00           | .14  | .35  | 1,200      | C-2V          |
| CM159       | 6.30           | .15  | .34  | 5,000      | C-2R          |
| CM259       | 6.30           | .25  | .65  | 5,000      | C-2R          |
| CM444       | 6.30           | .25  | .90  | 3,000      | C-2V          |
| CM447       | 6.30           | .15  | .52  | 1,500      | C-2V          |
| CM555       | 6.30           | .25  | .90  | 3,000      | C-2R          |
| CM147       | 7.00           | .43  | 2.0  | 1,500      | C-2R          |
| CM190       | 7.00           | .34  | .30  | 25,000     | C-2F          |
| CM947       | 9.84           | .50  | 4.0  | 200        | C-2R          |
| CM280       | 10.0           | .13  | .85  | 250        | C-2V          |
| CM3-501     | 12.0           | .42  | 2.6  | 1,000      | C-2R          |
| CM3-504     | 12.0           | .25  | 1.11 | 4,000      | C-2V          |
| CM3-509     | 12.0           | .17  | .80  | 4,000      | C-2V          |
| CM192       | 13.0           | .33  | 3.0  | 1,000      | C-2V          |
| CM124       | 14.0           | .27  | 1.5  | 5,000      | C-2F          |
| CM158       | 14.0           | .24  | 2.0  | 500        | C-2V          |
| CM161       | 14.0           | .19  | 1.0  | 1,500      | C-2F          |
| CM168       | 14.0           | .35  | 3.0  | 1,500      | C-2F          |
| CM193       | 14.0           | .33  | 2.0  | 5,000      | C-2F          |
| CM194       | 14.0           | .27  | 2.0  | 1,500      | C-2F          |
| CM658       | 14.0           | .08  | .31  | 15,000     | C-2F          |
| CM184       | 14.4           | .24  | 1.0  | 5,000      | C-2F          |
| CM3-505     | 24.0           | .13  | 1.0  | 5,000      | C-2F          |
| CM3-507     | 24.0           | .21  | 2.4  | 5,000      | C-2F          |
| CM152       | 28.0           | .07  | .85  | 10,000     | C-2F          |
| CM400       | 28.0           | .10  | 1.6  | 1,000      | C-2V          |
| CM464       | 28.0           | .17  | 3.0  | 1,500      | C-2F          |
| CM585       | 28.0           | .04  | .30  | 7,000      | C-2F          |
| CM655       | 28.0           | .20  | 3.0  | 7,000      | C-2F          |
| CM656       | 28.0           | .06  | .62  | 2,500      | C-2F          |
| CM657       | 28.0           | .08  | .62  | 7,500      | C-2F          |

Chicago Miniature Lamp reserves the right to make specification revisions that enhance the design and/or performance of the product