


p r o d u c t d a t a



Z-Type Markers

The Z-type cable marker has been designed to allow each size of marker to fit a wide range of cable diameters.

- ***Gusseted design allows marker to fit firmly over a wide range of cable diameters***
- ***9 sizes for cables from <0.5mm² to 35mm²***
- ***Clear, legible mark***
- ***Choice of straight or chevron cut***
- ***Colour coded option***

From the widely differing environments of an offshore platform to a control panel, Critchley have developed an extensive range of marking systems to suit a variety of identification requirements.

Z-Type Markers

FOR CABLE DIAMETER mm	FOR CABLE SIZE mm ² (BS6004)(BS6231)	MARKER SIZE	MARKER LENGTH mm	PACKED REEL (R) BOX (A)	PANCAKE REEL (PR)	ORDER CODE (Straight cut)	ORDER CODE (Chevron cut)
1.5-2.0	-	5	4.5	1000	-	0580	1151
2.0-3.2	1.0	7	4.5	1000	-	0581	1152
2.5-4.0	1.5	9	4.5	1000	250	0615	1153
2.9-4.7	2.5	11	4.5	1000	250	0616	1154
3.4-5.7	4.0	13	4.5	1000	200	0617	1155
3.8-6.3	6.0	15	4.5	1000	150	0618	1156
4.3-6.9	10.0	18	4.5	500	150	0620	1157
5.5-8.9	16.0	23	6.0	500	75	0622	1158
7.9-12.7	25.0	35	6.0	250	50	0624	1159

MATERIAL
PVC

COLOUR OPTIONS
STRAIGHT CUT:

White body marked black:
A-Z, 0-9 and symbols, available on reels (R) in boxes (A) and on pancake reels (PR).

Yellow body marked black:
A-Z, 0-9 and symbols, available on reels (R) only.
COLOUR CODED:
0-9 all sizes, available in boxes (A). 0-9 box pack (100 off each number) also available.

CHEVRON CUT:

White body marked black:
A-Z, 0-9 and symbols, available in boxes (A) only.

Yellow body marked black:
A-Z, 0-9 and symbols, available on reels (R) only.

COLOUR CODED:
0-9, size 11 only, available in boxes (A) or on reels (R).

SERVICE TEMPERATURE
-45°C to +70°C

CHEMICAL RESISTANCE
Excellent resistance to sea water, detergents (10% aqueous), fuels, oils, white and industrial spirit.

APPLICATORS FOR Z-TYPE CABLE MARKERS

SIZE	Z-TYPE SIZE	PACKED	ORDER CODE
1	7	1	1251
2	9	1	1252
3	11	1	1253
4	13	1	1254
5	15	1	1255
6	18	1	1256

CABLE DIAMETER

mm	0.5	1.0	2.0	3.0	4.0	5.0	6.0	7.0	8.0	9.0	10.0	11.0	12.0	13.0	14.0	15.0
Cable size mm ²			1.0	1.5	2.5	4.0	6.0	10.0	16.0	25	35	50	70			
5																
7																
9																
11																
13																
15																
18																
23																
35																