

High-performance Differential Probes

P7350 • P7330 • P6330 Data Sheet



Features & Benefits

- <100 ps Rise Time (P7350 guaranteed)
- 5 GHz to 3.5 GHz Bandwidths (typical)
- Low Input Capacitance:
 - <0.3 pF Differential (P7350 typical)
- ≥ 60 dB (1000:1) Common Mode Rejection Ratio (CMRR) at 1 MHz (P7330, P6330 typical)
- Small Probe Head Allows Easy Probing of SMDs

Applications

- Communications (Gigabit Ethernet, Fibre Channel, InfiniBand)
- Semiconductor Characterization and Validation
 - PCI Express
 - Serial ATA
 - IEEE 1394
 - USB 2.0 (The P7350 is not recommended for USB 2.0 compliance testing)
 - RAMBUS
 - DDR
- Disk Drive Design

Tektronix' proven expertise in probes brings you the highest fidelity in high-speed differential probing. The P7350, P7330, and P6330 high-bandwidth differential probes offer excellent signal fidelity, meeting the needs of engineers in design and debug of technologies with very fast clock speeds and edge rates. They provide high-bandwidth, low circuit loading, low-noise differential probing solutions for high-speed circuit designers.

P7350

The P7350 improves usability with variable spacing and solder-down capability, and a small form factor for ease of use on densely packed circuit boards with difficult-to-reach probe points. It employs the patented TekConnect® interface, which preserves signal integrity to 10 GHz and beyond to meet present and future bandwidth needs.

P7330 and P6330

The P7330 and P6330 enable users to make time-domain or frequency-domain measurements on high-bandwidth signals commonly found in digital IC designs, communication applications, and disk drive applications. The P7330 and P6330 provide high-bandwidth, low circuit loading, and low-noise differential probing solutions. The small probe head geometry and assorted probe tip accessories allow these probes to easily accommodate manual probing of surface-mount devices.

Performance You Can Count On

Depend on Tektronix to provide you with performance you can count on. In addition to industry-leading service and support, this product comes backed by a one-year warranty as standard.

Characteristics

Characteristic	P7350	P7330	P6330
Rise Time	<100 ps (guaranteed)	<140 ps (guaranteed)	<140 ps (guaranteed)
Bandwidth	5.0 GHz	3.5 GHz	3.5 GHz
Attenuation	6.25x	5x	5x
Differential Input C		<0.3 pF (typical)	
Differential Input Resistance	100 k Ω	100 k Ω	100 k Ω
Differential Input Range	± 2.5 V (20 °C to 30 °C)	± 2 V (20 °C to 30 °C)	± 2 V (20 °C to 30 °C)
Common Mode Input Range	+6.25 V to -5 V	+5 V to -4 V	+5 V to -4 V
Max Voltage (nondestruct)	± 25 V (DC + peak AC)	± 25 V (DC + peak AC)	± 25 V (DC + peak AC)
CMRR	>45 dB at 1 MHz (typical)	>60 dB at 1 MHz (typical)	>60 dB at 1 MHz (typical)
Noise	Approx. 46 nV/root Hz	Approx. 35 nV/root Hz	Approx. 35 nV/root Hz
Interface	TekConnect	TekConnect	TEKPROBE II BNC
Cable Length	1.3 m	1.3 m	1.3 m

Ordering Information

P7350

5.0 GHz Differential Probe for TekConnect Interface.
Supports CSA/TDS8200, CSA/TDS8000, TDS/CSA7000/B, and TDS6000/B/C Series.*1

P7330

3.5 GHz Differential Probe for TekConnect Interface.
Supports CSA/TDS8200, CSA/TDS8000, TDS/CSA7000/B, and TDS6000/B/C Series.*1

P6330

3.5 GHz Differential Probe for TEKPROBE® BNC Interface.
Supports TDS/CSA7000/B, TDS6000/B/C, TDS700, TDS600 Series.*2

All Include: One-year warranty, plus see Accessories table below.

*1 CSA/TDS8200, CSA/TDS8000 Series requires the use of the 80A03 TekConnect Interface Adapter.

*2 TDS6000/B/C or TekConnect TDS7000/B Series oscilloscopes require a TCA-BNC adapter.

Accessories

Accessory	P7350		P7330		P6330	
	Part No.	Quantity	Part No.	Quantity	Part No.	Quantity
Y Lead Adapter	196-3434-xx	2 each	196-3434-xx	2 each	196-3434-xx	2 each
3 in. Ground Lead	196-3469-xx	2 each	196-3469-xx	2 each	196-3469-xx	2 each
SMT KlipChip™ Adapter	206-0364-xx	2 each	206-0364-xx	2 each	206-0364-xx	2 each
TwinFoot™ Adapter (Pkg of 2)	016-1785-xx	1 pkg	016-1785-xx	1 pkg	016-1785-xx	1 pkg
Square Pin Adapter (Pkg of 4)	016-1884-xx	1 pkg	016-1884-xx	1 pkg	016-1884-xx	1 pkg
Plastic Accessory Box	006-7164-xx	1	006-7164-xx	1	006-7164-xx	1
Coding Color Marker Kit	016-1886-xx	1	—	—	—	—
Color-coding Clips	—	—	016-1315-xx	1 set	016-1315-xx	1 set
Variable Spacing Adapter (pkg of 4)	016-1885-xx	1 pkg	016-1885-xx	1 pkg	016-1885-xx	1 pkg
Probe Carrying Case	016-1879-xx	1	016-1879-xx	1	016-1879-xx	1
Instruction Manual	071-1238-xx	1	071-0758-xx	1	071-0757-xx	1
Certificate of Traceable Calibration	—	1	—	1	—	1
Antistatic Wrist Strap	006-3415-04	1	006-3415-04	1	006-3415-04	1
Pin Jumper Lead	196-3473-xx	2	196-3473-xx	2	196-3473-xx	2
Solder In Kit	020-2505-xx	1	—	—	—	—

Service

Opt. C3 – Calibration Service 3 Years.

Opt. C5 – Calibration Service 5 Years.

Opt. D1 – Calibration Data Report.

Opt. D3 – Calibration Data Report 3 Years (with Opt. C3).

Opt. D5 – Calibration Data Report 5 Years (with Opt. C5).

Opt. G3 – Complete Care 3 Years (includes loaner, scheduled calibration and more).
P7330, P7350 only

Opt. G5 – Complete Care 5 Years (includes loaner, scheduled calibration and more).
P7330, P7350 only

Opt. R3 – Repair Service 3 Years.

Opt. R5 – Repair Service 5 Years.

Recommended Accessories

IEEE 1394 Breakout Connector – Order 679-5027-xx.

IC Grabber – Order 013-0309-xx (Pkg of 2).

Related Products

1103 – TEKPROBE® II power supply for interfacing with other BNC instruments

80A03 – TekConnect probe interface module for TDS/CSA8000 Series oscilloscopes.

Power Plug Options for 1103

A0 – North America power.

A1 – Universal EURO power.

A2 – United Kingdom power.

A3 – Australia power.

A4 – 240 V, North America power.

A5 – Switzerland power.

CE Marking Not Applicable.



Tektronix is registered to ISO 9001 and ISO 14001 by SRI Quality System Registrar.

Contact Tektronix:

- ASEAN / Australasia (65) 6356 3900
- Austria 00800 2255 4835*
- Balkans, Israel, South Africa and other ISE Countries +41 52 675 3777
- Belgium 00800 2255 4835*
- Brazil +55 (11) 3759 7627
- Canada 1 800 833 9200
- Central East Europe and the Baltics +41 52 675 3777
- Central Europe & Greece +41 52 675 3777
- Denmark +45 80 88 1401
- Finland +41 52 675 3777
- France 00800 2255 4835*
- Germany 00800 2255 4835*
- Hong Kong 400 820 5835
- India 000 800 650 1835
- Italy 00800 2255 4835*
- Japan 81 (3) 6714 3010
- Luxembourg +41 52 675 3777
- Mexico, Central/South America & Caribbean 52 (55) 56 04 50 90
- Middle East, Asia, and North Africa +41 52 675 3777
- The Netherlands 00800 2255 4835*
- Norway 800 16098
- People's Republic of China 400 820 5835
- Poland +41 52 675 3777
- Portugal 80 08 12370
- Republic of Korea 001 800 8255 2835
- Russia & CIS +7 (495) 7484900
- South Africa +41 52 675 3777
- Spain 00800 2255 4835*
- Sweden 00800 2255 4835*
- Switzerland 00800 2255 4835*
- Taiwan 886 (2) 2722 9622
- United Kingdom & Ireland 00800 2255 4835*
- USA 1 800 833 9200

* European toll-free number. If not accessible, call: +41 52 675 3777

Updated 10 February 2011

For Further Information. Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit www.tektronix.com



Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.

02 Oct 2011

60W-13756-12

