

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0534011110
Status: Obsolete
Description: 2.00mm (.079") Pitch Wire-to-Board Header, Vertical, with Kinked PC Tail, 11 Circuits

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Headers
Series 53401
Application Signal, Wire-to-Board
Product Name N/A

Physical

Breakaway No
Circuits (Loaded) 11
Circuits (maximum) 11
Durability (mating cycles max) 30
Flammability 94V-0
Glow-Wire Compliant No
Lock to Mating Part Yes
Number of Rows 1
Orientation Vertical
PC Tail Length 3.50mm (.138")
PCB Locator No
PCB Retention Yes
PCB Thickness - Recommended 1.60mm (.063")
Packaging Type Tray
Pitch - Mating Interface 2.00mm (.079")
Polarized to PCB No
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40°C to +105°C

Electrical

Current - Maximum per Contact 2A
Voltage - Maximum 125V

Material Info

Reference - Drawing Numbers

Product Specification PS-51090-004, PS-52484-009, PS-54299-001,
RPS-51090-005, RPS-51090-008, RPS-51090-012,
RPS-51090-014, RPS-52484-015, RPS-52484-016,
RPS-52484-017, RPS-52484-022, RPS-52484-023
Sales Drawing SD-53401-008

EU RoHS
Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[53401Series](#)

Mates With
[52484](#) , [51090](#)