


Ring Terminals Vinyl Insulated

159-2201 159-2202 159-2204 159-2206 159-2208 159-2210

KOBICONN

Ring Terminals Vinyl Insulated

159-2201 159-2202 159-2204 159-2206 159-2208 159-2210



Dimensions: In.

SPECIFICATIONS

Wire Range:	22-16 AWG
Maximum Current:	19A
Maximum Electrical Rating:	75°C 600 volts max.
Insulation Color:	Red
Terminal Material:	Copper, Thickness: .029 (0.75mm)
Insulation Material:	Vinyl

Mouser Stock No.	Dimensions (In.)							
	StudSize	W	L	F	B	D	C	
159-2201	1/4	.251	.457	1.083	.437			
159-2202	5/16	.330	.457	1.083	.437			
159-2204	4	.125	.224	.701	.194			
159-2206	6	.145	.224	.701	.194	.394	.134	.067
159-2208	8	.169	.314	.847	.275			
159-2210	10	.208	.314	.847	.275			

Date Last Revised: 6/21/12

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300028

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[159-2202](#) [159-2210](#) [159-2208](#) [159-2204](#) [159-2201](#) [159-2206](#)