



380 / 381 / 383 / 384 Non-Contact Thermometer

APPLICATIONS

HVAC/R:

Compressor heads, vents, insulation, leaks around cooler or freezer doors, steam traps, registers

Food:

Grill & surface temperatures, holding cabinets, serving temperatures, storage temperatures

Electrical:

Cables, circuit breakers, connections, machinery, motors, transformers

Turn over for
technical
information
and accessory
part numbers.

The
Value
Leader™

Measure Hard-to-reach, sensitive, or large moving target areas.



380 • 381 • 383



High Temperature
Model 384

Measure Hard-to-reach, sensitive, or large moving target areas. Use the 380, 381, and 383 to measure surface temperature and watch the LCD immediately display accurate data without the use of a probe.

- Easy to use single button operation
- 0.1 resolution for best reading (380/381)
- Last reading hold
- Soft holster pouch included
- 8:1 distance to spot ratio
- Large, easy to read display
- °C and °F selectable
- 9V battery included
- Temperature range:
 - 380/381: -4°F to 572°F
(-20°C to 300°C)
 - 383: -31°F to 999°F
(-35°C to 560°C)
 - 384: -4°F to 1,832°F
(-20°C to 1,000°C)

Model 380 (no laser) **Model 381** (with laser)
Model 383 (with laser) **Model 384** (with laser)



TECHNICAL SPECIFICATIONS AND ACCESSORIES

- Digital Multimeters
- Clamp Meters
- Hand-held Oscilloscopes
- Refrigerant & Combustible Gas
- Leak Detectors
- Temperature Testers
- BNC
- Coax Cable Connectors
- Test Leads
- Accessories

Test Products International, Inc.
Headquarters:
9615 SW Allen Blvd.
Beaverton, OR 97005
USA
503-520-9197
Fax: 503-520-1225
email:
info@tpi-thevalueleader.com

Test Products International, Ltd.
342 Bronte St. South
Unit 9
Milton, Ontario L9T
5B7
Canada
905-693-8558
Fax: 905-693-0888
email:
info@tpicanada.com

Test Products International UK Ltd.
Longley House, East Park
Crawley, West Sussex
RH10 6AP England
Tel: +44 (0)1293 561212
Fax: +44 (0)1293813465
contactus@tpieurope.com

380 / 381 / 383 / 384 Non-Contact Thermometer

SPECIFICATIONS

Temperature Range (380/381):	-20°C ~ 300°C (-4°F ~ 572°F)
(383):	-35°C ~ 560°C (-31°F ~ 999°F)
(384):	-20°C ~ 1,000°C (-4°F ~ 1,832°F)
Accuracy	±2% or ±2°C or ±3°F whichever is greater
Repeatability	±2% of reading, or ±2°C, whichever is greater
Response Time	500 m Second
Spectral Response	7µm ~ 14µm
Emmisivity : Fixed	0.95
Distance to Spot Size	8:1
Laser Sighting	380: no laser 381: with laser
°C/°F Select	Yes
Display	4 digits
Display Resolution (380/381):	0.1
(383):	-35°C ~ 299°C : 0.1°C (0.1°F) 300°C ~ 560°C : 1°C (1°F)
Display Hold	Last reading display for 7 sec.
Low Battery Detection	Yes
Back Light	Yes
Operating Temperature	0°C ~ 50°C
Storage Temperature	-25°C ~ 70°C without battery
Relative Humidity	10% ~ 95%
Weight	7oz (200g)
Dimension	155mm x 127mm x 35mm
Power	9V Alkaline or NiCd battery

Distributed By:



To learn about the entire
line of TPI products visit:

www.tpi-thevalueleader.com

L 380 SERIES-0905

Copyright © 2005 Test Products International, Inc.

FAQ

What does “distance to spot ratio” mean?

The laser spot needs to be showing inside the target area. An 8:1 “distance to spot ratio” means you are measuring a 1” diameter area at a distance of 8”.

How far can I measure?

Distance is unlimited. The size of the target area sets the limit on distance for accurate measurements. Example: If the area you wish to measure is 1 foot in diameter, then you will need to be within 8 feet to record an accurate temperature.

What is the smallest target I can read?

Approximately one-half inch in diameter.

What is emmisivity?

This is a ratio of an object's infrared emission compared to a theoretical black body considered 1. Emissivity is always less than 1. Adjustable emissivity allows your non-contact thermometer to be adjusted to the surface you are checking to make readings more accurate.