Pomona®

Model 3925 & Kits 4176-02 & 5522 Do-It-Yourself Minigrabber® Test Clip



MATERIALS:
Body: Contact – Gold Plated Beryllium Copper, Spring – Stainless Steel
Insulation: Glass filled nylon.
Marking: "Pomona 3925"

RATINGS:
Operating Voltage: Hand-held testing: 30VAC/60VDC Max.
Hands free testing in controlled voltage environments: 300 WVDC Max.
Operating Temperature: +102º(+216ºF.) Max.
Current: 5 Amperes

ORDERING INFORMATION: Model 3925, 4176-02 & 5522
Standard Colors: Available in 10 colors: -0 Black, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White
Kit 5522 contains 10 pieces of 3925, one of each color.
Kit 4176-02 contains 2 pieces of 3925, one Black / one Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (,51 mm), .xxx = ± .005" (,127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

Pomona*ACCESS* **90221** (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com