


# Bat Handle Toggle



| NTE Type No. | Circuitry | Action |      |     | Actuator           | Diag No. |
|--------------|-----------|--------|------|-----|--------------------|----------|
| 54-057       | DPST      | ON     | NONE | OFF | Brass/Nickel Plate | S9       |




## Specifications

**Current Rating:** 20A 125VAC, 10A 250VAC, 1 1/2 HP 125-250VAC  
**Insulation Resistance:** 100 Megohms (min.)  
**Dielectric Strength:** 1000V RMS (min.)  
**Temperature Rating:** 0°F to +150°F (-17.8°C to +65.6°C)  
**Electrical Life:** 25,000 cycles  
**Mechanical Life:** 100,000 cycles  
**Terminal Type:** Screw Type  
**Mounting Hole:** .500 (12.7)

# Bat Handle Toggle



| NTE Type No. | Circuitry | Action |      |     | Actuator           | Diag No. |
|--------------|-----------|--------|------|-----|--------------------|----------|
| 54-026       | DPST      | ON     | NONE | OFF | Brass/Nickel Plate | S8       |
| 54-027       | DPDT      | ON     | NONE | ON  | Brass/Nickel Plate | S8       |
| 54-028       | DPDT      | ON     | OFF  | ON  | Brass/Nickel Plate | S8       |



## Specifications

**Current Rating:** 15A 125VAC, 10A 250VAC, 3/4 HP 125-250VAC  
**Insulation Resistance:** 100 Megohms (min.)  
**Dielectric Strength:** 1000V RMS (min.)  
**Temperature Rating:** +32°F to +185°F (0°C to +85°C)  
**Electrical Life:** 50,000 cycles  
**Mechanical Life:** 100,000 cycles  
**Terminal Type:** "3-in-1" Combi-Terminal  
**Mounting Hole:** .500 (12.7)