

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [34826-0125](#)
Status: **Active**
Overview: Mini50™ Unsealed Connection Systems
Description: Mini50™ Unsealed, Dual Row, Right-Angle Header, 12 Circuit, Polarization Option B, Gray, Tray

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	PCB Headers
Series	34826
Application	Power, Signal, Wire-to-Board
Overview	Mini50™ Unsealed Connection Systems
Product Name	Mini50™
UPC	887191338354

Physical	
Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	Polyester Alloy
Net Weight	2.414/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.90mm
PCB Locator	Yes
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount

Electrical	
Current - Maximum per Contact	3A
Voltage - Maximum	500V

Material Info

Reference - Drawing Numbers	
Sales Drawing	SD-34826-001

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[34826Series](#)

Mates With
[34824](#) Mini50™ Unsealed Dual Row Receptacle

Use With
[560023](#) CTX50 Receptacle Terminal Unsealed