



Industrial Adhesives & Tapes

3M™ Fastener SJ3402 Hook Tan, 1 in x 50 yd 0.15 in Engaged Thickness, 12 per case Bulk

3M ID 70006701364 UPC# 00051128759394 Part Number SJ3402 3M Product Number SJ3402



3M™ Fastener SJ3402 is a non-adhesive nylon hook fastener, with temperature resistance of up to 200 degrees fahrenheit and 100 mils to 150 mils ofengaged thickness.

- Tan colored hook fastener designed for matching fabric, upholstery, clothing and uniforms.
- Woven nylon is durable for thousands of closures.
- Aerospace, Electronics, Construction, Specialty Vehicle, Military, Medical, Furniture, General Industrial
- Securing Fabric to Furniture Cushions, Airplane Seating, Carpet Panel Attachments, Uniforms, Gloves and Clothing



Overview

3M™ Fastener SJ3402 provides a tailored appearance for garments and fabrics and allows for adjustable closure. 3M™ Fastener SJ3402 is washable and dry cleanable. It is preshrunk to ensure maximum dimensional stability and flatness.

Specifications

Adhesive Type	Non Adhesive
Brand	3M
Closure Life	5000
Color	Tan
Engaged Thickness	0.15 Inch
Flame Retardant	No
Hook/Loop	Hook
Industries	Transportation, Specialty Vehicle, Construction, Furniture, Medical, Military & Government, General Industrial, Electronics
Length	50 Linear Yard
Length (Metric)	45.72 m
Low Profile	No
Material	Nylon
Maximum Operating	93 Degree Celsius

Temperature (Celsius)	
Maximum Operating Temperature (Fahrenheit)	200 Degree Fahrenheit
Product Form	Roll
Width	1 Inch
Width (Metric)	25.4 mm