





REV. C
DCO 300853

TOLERANCES $\pm .010$ " - UNLESS
OTHERWISE SPECIFIED

COIL: @ 25°C
RESISTANCE 70 OHMS $\pm 10\%$
NOMINAL VOLTAGE 12 VDC
MUST OPERATE 6.9 VDC MAX.
MUST RELEASE 3.3 VDC MAX., 0.75 VDC MIN.

ENVIRONMENT:
VIBRATION 33 Hz TO 3000 Hz @ 30 g's
SHOCK 200 g's 6 MS. DURATION
TEMPERATURE -70 °C TO +125 °C
NOTES: OPERATE, RELEASE 15 MS MAX.
CONTACT BOUNCE 1 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING:
25 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE
50,000 OPERATIONS

DR. B.D. 10APR2008 CK. J.M.B. 5/14/08

Tyco Electronics

©COPYRIGHT 2005
TYCO ELECTRONICS CORPORATION
ALL INTERNATIONAL RIGHTS RESERVED

CUST. CATALOG
CUST. NO. REV. N/A

TE NUMBER
4-1617753-5

CII PART NUMBER
FCA-325-BY2