

Search within category

GO

BUY NOW

DESIGN / INSTALL



VB0B1L4BT24M1

The 30A, 208V vertical power strip in black has 24 IEC C-13 receptacles. It features four 15A thermal breakers and a 10' (3m) power cord with a NEMA L6-30P twist-lock plug. It is UL and c-UL listed and measures 66.3H x 1.7W x 1.7D (1683mm x 44mm x 44mm). The breaker doghouse adds 1.44 (87.4mm) to the overall depth. It is sold individually.

This part number has been obsoleted with no replacement. [Click here](#) to contact customer service for further assistance.

Specs

Packaging Details

Documents

OM Obsolete Code	OBSOLETE
Rack PDU Type	Basic Rack PDU
Monitoring	NA
Remote Outlet Switching	No
Mount Orientation	Vertical
Current Rating (Amps)	30A
Input Voltage	208V - Single Phase
Plug Type	NEMA L6-30P
Output Voltage	208V
Receptacle Type	IEC C-13
Total Number of Outlets	24
Depth (In.)	1.61
Depth (mm)	40.9
Height (In.)	66.25
Height (mm)	1682.8
Width (In.)	1.72
Width (mm)	43.7
Tool-Less Button Spacing (In.)	64.75
Tool-Less Button Spacing (mm)	1644.7
No. of Rack Spaces	0
Surge Suppression	No
Amps	30A
Cable Length	3
Input Power Range (kW)	1.0-5.0kW
Length (In.)	68.00
UL Recognized	Yes
Voltage	208V
RoHS Compliancy Status	Compliant
Min. Order Qty.	1