




Protection: 4 --> flash AU
6 --> 0.76μ AU

LEAD FREE PART NUMBER

Protection: 4 --> flash AU
6 --> 0.76 μ AU

Pitch 2.76 (shell 25-37)
Pitch 2.74 (shell 09-15)

holes Ø0.90 mini

±0.10

Ø3.10

Ø0.13

1.37 (shell 09-15)
1.38 (shell 25-37)

E

B

1.42

1.42

0 50 100 mm

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:	
SEE DRAWING C01-8646-0000	

European Views

rev	ecn no	dr	date
B	-	ATC	2000/12/28
C	LS05-001	MPE	2005/03/14
D	LS05-0056	MPE	2005/06/30
E	LS06-0097	LGO	2006/07/28
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	MASSON	2000/07/26	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	2000/07/26			0.XX	±0.1				
Chr	LEGARE	2000/07/26			0.XXX	±0.1				
Appr	LEGARE	2000/07/26	Product family		D-SUB		Spec ref -			
			title FEMALE CONNECTOR FOR FOOT STRAIGHT SOLDER TYPE FOR			dwg no C01-8646-0717			Rev. E	
catalog no			-			CUSTOMER			sheet	of 1