

Heavy Duty AC Rated Toggle Switches

General Purpose switches rated at 15 amps, 125 VAC and 28 VDC and 10 amps at 250 VAC. UL listed and CSA certified in single, double, three and four pole configurations. All are rated 3/4 H.P. — 15/32" bushing — 11/16" Toggle.

| Stock No.                        | Mfr.'s Type                            | Switch Action                                                      | Terminals                | EACH                    |                         |                         |                         |
|----------------------------------|----------------------------------------|--------------------------------------------------------------------|--------------------------|-------------------------|-------------------------|-------------------------|-------------------------|
|                                  |                                        |                                                                    |                          | 1-24                    | 25-99                   | 100-499                 | 500-999                 |
| 683-0048<br>683-0049             | 2FA53-73<br>2FA53-73-TABS              | S.P.S.T. ON-NONE-OFF<br>S.P.S.T. ON-NONE-OFF                       | Solder<br>Spade          | 3.59<br>3.59            | 2.77<br>2.77            | 2.43<br>2.43            | 2.13<br>2.13            |
| 683-0050<br>683-0051<br>683-0052 | 2FA54-73<br>2FB53-73<br>2FB53-73-TABS  | S.P.S.T. ON-NONE-OFF<br>S.P.D.T. ON-NONE-ON<br>S.P.D.T. ON-NONE-ON | Screw<br>Solder<br>Spade | 4.11<br>4.41<br>4.41    | 3.18<br>3.43<br>3.43    | 2.79<br>3.01<br>3.01    | 2.79<br>2.64<br>2.64    |
| 683-0053<br>683-0054             | 2FB54-73<br>2FC53-73                   | S.P.D.T. ON-NONE-ON<br>S.P.D.T. ON-OFF-ON                          | Screw<br>Solder          | 5.19<br>4.41            | 4.02<br>3.43            | 3.53<br>3.01            | 3.09<br>2.64            |
| 683-0055<br>683-0056<br>683-0057 | 2FC53-73-TABS<br>2FC54-73<br>6FC54-73* | S.P.D.T. ON-OFF-ON<br>S.P.D.T. ON-OFF-ON<br>S.P.D.T. ON-OFF-ON     | Spade<br>Screw<br>Screw  | 4.41<br>5.19<br>7.22    | 3.43<br>4.02<br>5.59    | 3.01<br>3.53<br>4.90    | 2.64<br>3.09<br>4.30    |
| 683-0058<br>683-0059             | 2GK50-73<br>2GK51-73                   | D.P.S.T. ON-NONE-OFF<br>D.P.S.T. ON-NONE-OFF                       | Solder<br>Spade          | 5.68<br>5.68            | 4.41<br>4.41            | 3.87<br>3.87            | 3.39<br>3.39            |
| 683-0060<br>683-0061<br>683-0062 | 2GK54-73<br>2GL50-73<br>2GL51-73       | D.P.S.T. ON-NONE-OFF<br>D.P.D.T. ON-NONE-ON<br>D.P.D.T. ON-NONE-ON | Screw<br>Solder<br>Spade | 6.73<br>6.79<br>6.79    | 5.22<br>5.26<br>5.26    | 4.58<br>4.62<br>4.62    | 4.02<br>4.05<br>4.05    |
| 683-0063<br>683-0064             | 2GL54-73<br>2GM50-73                   | D.P.D.T. ON-NONE-ON<br>D.P.D.T. ON-OFF-ON                          | Screw<br>Solder          | 8.34<br>6.79            | 6.47<br>5.26            | 5.67<br>4.62            | 4.97<br>4.05            |
| 683-0065<br>683-0066<br>683-0067 | 2GM51-73<br>2GM54-73<br>HK250-73       | D.P.D.T. ON-OFF-ON<br>D.P.D.T. ON-OFF-ON<br>3.P.S.T. ON-NONE-OFF   | Spade<br>Screw<br>Solder | 6.79<br>8.34<br>10.43   | 5.26<br>6.47<br>8.08    | 4.62<br>5.67<br>7.09    | 4.05<br>4.97<br>6.21    |
| 683-0068<br>683-0069             | HK251-73<br>HK254-73                   | 3.P.S.T. ON-NONE-OFF<br>3.P.S.T. ON-NONE-OFF                       | Spade<br>Screw           | 10.43<br>12.34          | 8.08<br>9.57            | 7.09<br>8.39            | 6.21<br>7.36            |
| 683-0070<br>683-0071<br>683-0072 | HL250-73<br>HL251-73<br>HL254-73       | 3.P.D.T. ON-NONE-ON<br>3.P.D.T. ON-NONE-ON<br>3.P.D.T. ON-NONE-ON  | Solder<br>Spade<br>Screw | 12.82<br>12.82<br>15.34 | 9.93<br>9.93<br>11.89   | 8.71<br>8.71<br>10.43   | 7.64<br>7.64<br>9.15    |
| 683-0073<br>683-0074             | HM250-73<br>HM251-73                   | 3.P.D.T. ON-OFF-ON<br>3.P.D.T. ON-OFF-ON                           | Solder<br>Spade          | 12.82<br>12.82          | 9.93<br>9.93            | 8.71<br>8.71            | 7.64<br>7.64            |
| 683-0075<br>683-0076<br>683-0077 | HM254-73<br>IK250-73<br>IK251-73       | 3.P.D.T. ON-OFF-ON<br>4.P.D.T. ON-NONE-OFF<br>4.P.S.T. ON-NONE-OFF | Screw<br>Solder<br>Spade | 15.34<br>14.30<br>14.30 | 11.89<br>11.08<br>11.08 | 10.43<br>9.72<br>9.72   | 9.15<br>8.52<br>8.52    |
| 683-0078<br>683-0079             | IK254-73<br>IL250-73                   | 4.P.S.T. ON-NONE-OFF<br>4.P.D.T. ON-NONE-ON                        | Screw<br>Solder          | 15.87<br>17.46          | 12.30<br>13.53          | 10.79<br>11.86          | 9.46<br>10.40           |
| 683-0080<br>683-0081<br>683-0082 | IL251-73<br>IL254-73<br>IM250-73       | 4.P.D.T. ON-NONE-ON<br>4.P.D.T. ON-NONE-ON<br>4.P.D.T. ON-OFF-ON   | Spade<br>Screw<br>Solder | 17.46<br>20.99<br>17.46 | 13.53<br>16.28<br>13.53 | 11.86<br>14.28<br>11.86 | 10.40<br>12.52<br>10.40 |
| 683-0083<br>683-0084             | IM251-73<br>IM254-73                   | 4.P.D.T. ON-OFF-ON<br>4.P.D.T. ON-OFF-ON                           | Spade<br>Screw           | 17.46<br>20.99          | 13.53<br>16.28          | 11.86<br>14.28          | 10.40<br>12.52          |

\*Momentary on action.

Nylon Insulated Toggle Switches


Series D switches have self-cleaning wiping action contacts suitable for both power and low-level switching nylon flat or bat lever actuators and bushing/frame super structure for double insulated requirements. UL listed, CSA certified. Series rated at 10 amps 125 VAC, 5 amps 250 VAC, 1/2 H.P. 125-250 VAC, 10 amps 28 VDC.

Paddle Toggle Actuator

| Stock No.                                    | Mfr.'s Type                                          | Switch Action                                                                             | Terminals                                            | EACH                         |                              |                              |                              |
|----------------------------------------------|------------------------------------------------------|-------------------------------------------------------------------------------------------|------------------------------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|
|                                              |                                                      |                                                                                           |                                                      | 1-24                         | 25-99                        | 100-499                      | 500-999                      |
| 683-0085<br>683-0086<br>683-0087<br>683-0088 | DA100-PB-B<br>DA105-PB-B<br>DB100-PB-B<br>DC100-PB-B | S.P.S.T. ON-NONE-OFF<br>S.P.S.T. ON-NONE-OFF<br>S.P.D.T. ON-NONE-ON<br>S.P.D.T. ON-OFF-ON | Solder/Spade<br>Wire<br>Solder/Spade<br>Solder/Spade | 2.44<br>3.57<br>2.73<br>2.73 | 1.90<br>2.77<br>2.12<br>2.12 | 1.66<br>2.43<br>1.86<br>1.86 | 1.46<br>2.13<br>1.63<br>1.63 |

Bat Toggle Actuator

|                      |                          |                                              |                      |              |              |              |              |
|----------------------|--------------------------|----------------------------------------------|----------------------|--------------|--------------|--------------|--------------|
| 683-0089<br>683-0090 | DA100-BB-B<br>DA105-BB-B | S.P.S.T. ON-NONE-OFF<br>S.P.S.T. ON-NONE-OFF | Solder/Spade<br>Wire | 2.44<br>3.57 | 1.90<br>2.77 | 1.66<br>2.43 | 1.46<br>2.13 |
|----------------------|--------------------------|----------------------------------------------|----------------------|--------------|--------------|--------------|--------------|



General Purpose Pushbutton Switches

Slow make/slow break momentary AC only. **Circuitry:** On-none-off. UL listed and CSA certified (P26A-1D-RND and P26L-1D-RND not shown).

6 Amps 125 VAC — 3 Amp 250 VAC

| Stock No.                                    | Mfr.'s Type                                      | Switch Action                                | Terminals                            | Cap                              | EACH                         |                              |                              |                              |
|----------------------------------------------|--------------------------------------------------|----------------------------------------------|--------------------------------------|----------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|
|                                              |                                                  |                                              |                                      |                                  | 1-24                         | 25-99                        | 100-499                      | 500-999                      |
| 683-0093<br>683-0094<br>683-0095<br>683-0097 | P26A-1D-RND<br>P26L-1D-RND<br>P27A-BL<br>P27L-BL | S.P.N.O.<br>S.P.N.C.<br>S.P.N.O.<br>S.P.N.C. | Solder<br>Solder<br>Solder<br>Solder | Metal<br>Metal<br>Black<br>Black | 5.48<br>5.48<br>4.93<br>4.93 | 4.24<br>4.24<br>3.81<br>3.81 | 3.72<br>3.72<br>3.35<br>3.35 | 3.26<br>3.26<br>2.93<br>2.93 |

15 Amps 125 VAC — 10 Amps 250 VAC

|                      |            |                      |                |                |              |              |              |              |
|----------------------|------------|----------------------|----------------|----------------|--------------|--------------|--------------|--------------|
| 683-0099<br>683-0100 | 170<br>172 | S.P.N.C.<br>S.P.N.O. | Screw<br>Screw | Metal<br>Metal | 8.65<br>8.65 | 6.71<br>6.71 | 5.89<br>5.89 | 5.16<br>5.16 |
|----------------------|------------|----------------------|----------------|----------------|--------------|--------------|--------------|--------------|

Quick Make/Quick Break Maintained AC/DC; 6 Amps 125 VAC — 3 Amps 250 VAC

|                      |                   |                      |               |                |              |              |              |              |
|----------------------|-------------------|----------------------|---------------|----------------|--------------|--------------|--------------|--------------|
| 683-0101<br>683-0102 | 110-SP<br>111-16P | S.P.S.T.<br>S.P.S.T. | Screw<br>Wire | Metal<br>Metal | 7.81<br>7.81 | 6.06<br>6.06 | 5.31<br>5.31 | 4.66<br>4.66 |
|----------------------|-------------------|----------------------|---------------|----------------|--------------|--------------|--------------|--------------|

