





MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
130010-0863	114030K12M005	1.64' +1.75" -0 [5M +44.5 -0]
130010-0864	114030K12M010	3.28' +2.19" -0 [1.0M +55.6 -0]
130010-0865	114030K12M020	6.56' +3.50" -0 [2.0M +88.9 -0]
130010-0866	114030K12M030	9.84' +3.50" -0 [3.0M +88.9 -0]
130010-0867	114030K12M040	13.12' +6.50" -0 [4.0M +165.1 -0]
130010-0868	114030K12M050	16.40' +6.50" -0 [5.0M +165.1 -0]
130010-0869	114030K12M060	19.68' +6.50" -0 [6.0M +165.1 -0]



MALE FACE VIEW

CENELEC EN 50 044
PINOUT SHOWN
(SAE-J-1738A PINOUT
SHOWN IN PARENTHESIS)

4 (1)	BLACK	4 (1)
3 (2)	BLUE	3 (2)
1 (3)	BROWN	1 (3)
2 (4)	WHITE	2 (4)

WIRING DIAGRAM

ITEM	COMPONENT	MATERIAL	FINISH
------	-----------	----------	--------

1	INSERT	PVC	YELLOW
---	--------	-----	--------

2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
---	----------------	--------------	------------------

3	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL
---	-------------	--------------	------------------

4	COUPLING NUT	ZINC DIE CAST	BLACK E-COATED
---	--------------	---------------	----------------

5	OVERMOLD	PVC	YELLOW
---	----------	-----	--------

6	CABLE- 16AWG, (65 X #34 COPPER STRANDING), 4 CONDUCTOR, 600V, TC-ER	TPE	YELLOW
---	---	-----	--------

7	LABEL	MYLAR	BLACK/YELLOW
---	-------	-------	--------------

QUALITY SYMBOL	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM	SCALE NONE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
	mm	INCH				
▼=0	4 PLACES	±---	±---	DRAWN BY LHARTMAN 2009/08/17	TITLE	MINI-CHANGE CORDSET 4 POLE MALE/FEMALE TPE CABLE
▼=0	3 PLACES	±---	±---			
▼=0	2 PLACES	±---	±.01			
▼=0	1 PLACE	±0.3	±---			
△=0	ANGULAR ±---°		APPROVED BY JFMURPHY 2010/01/14	DATE	molex	MOLEX INCORPORATED
△=0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					
△=0	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-130010-008	SHEET NO. 1 OF 1			
△=0	SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				