


MODEL - P2500PR

Type: Bench mounted
manual toggle press.


Nominal holding force:
2500 daN.

Weight: 15.50 kg.



With 17 daN handle force
the output force is:

Fully retracted	1000
10 mm extended	100
20 mm "	72
30 mm "	60
40 mm "	70
50 mm "	88
60 mm "	118
70 mm "	190
72 mm "	230
74 mm "	353
Fully extended	1100

**Quality Features:**


- S.G. Iron framecasting.
- precision ground steel plunger.
- fixed height work head.

MODEL TPR 1**MODEL - TPR 1**

Type: Bench mounted
toggle press

Nominal holding force:
500 daN

Weight: 9 kg





With 13 daN handle force
the output force is:

Fully retracted	48
5 mm extended	45
10 mm "	42
15 mm "	42
20 mm "	45
25 mm "	49
30 mm "	54
35 mm "	75
38 mm "	102
39 mm "	143
Fully extended	500

**Optional Extras: please
mention when ordering**

Table Bore 12 ^{H7}	mm	TB
Locking Device		VS
Stroke Counter		Z

**Quality Features:**

- hardened, ground ram.
- long-design, honed ram.
- ground table, with T-slot.
- adjustable working head height.