



CCS25-S8-C



- Durable nylon cable clamps

■ Part Number	CCS25-S8-C
■ RoHS Compliancy Status	Compliant
■ Part Description	Fixed Diameter Cable Clamp
■ Product Type	Mounting Device
■ Material	Nylon 6.6
■ Color	Natural
■ UL Recognized	E136577
■ Diameter (In.)	.17
■ Diameter (mm)	4.2
■ Width (In.)	.37
■ Width (mm)	9.4
■ Bundle Offset (mm)	10.4
■ Bundle Offset (In.)	.41
■ Environment	Indoors
■ Flammability Rating	UL94 V-2
■ Hole Diameter (In.)	.17
■ Hole Diameter (mm)	4.2
■ Max. Bundle Diameter (In.)	.25
■ Max. Bundle Diameter (mm)	6.3
■ Mounting Method	#8 (M4) Screw
■ Pricing Description	Fixed Dia Clamp, .25" (6.4mm) Bundle, #8 Screw (M4), WH
■ Screw Size	#8 (M4)
■ Screw Size Metric	M4
■ Type Of Application	Standard
■ Min. Order UOM	PC
■ Min. Order Qty.	100
■ BOM Qty. (# of Pkgs.)	