


Product specification

Product	CAT5E UTP SOLID 24AWG×4P		NO.	102286	Page	1/2
Edition		Established Date	2008-09-12	Revised Date	2010 11 4	
Approval	QINGBO	Checked		Finish	Lili	

Configuration & Physical Characters:

1. Conductor	Material	Bare Copper		
	Size	4×2×0.5mm .24AWG		
	Construction	1/0.50± 0.012		
2. Insulation	Material	HD-PE		
	Thickness	MIN at any point: 0.15mm MAX AVG:0.20 mm		
	Diameter	0.90 ± 0.01		
	Colors	Blue/White-Blue		
		Orange/White-Orange		
		Green/White-Green		
		Brown/White-Brown		
Elongation	MIN 300%			
Tensile strength	MIN 1.682Kg/mm ²			
3. Jacket	Material	PVC		 conductor insulation jacket rip cord
	Thickness	MIN at any point: 0.43mm MAX AVG: 0.48mm		
	Diameter	4.9 ± 0.2		
	Colors	Grey		
	Package length	220m/box		
4. Marking		Maxxtro NETWORK Cable UTP CAT.5E 24AWG ISO/IEC 11801 xxxxxxM		

Maxxtro®



Product specification

Product	CAT5E UTP SOLID 24AWG×4P		NO.	102286	Page	2/2
Edition		Established Date	2008-09-12	Revised Date	2010 11 4	
Approval	Q. ZHENG	Checked		Finish	Lili	

Electric Characters:

90m FLUKE P-LINK TEST