

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [50-57-9525](#)
Status: **Active**
Overview: [SL™ Modular Connectors](#)
Description: [SL™ Crimp Housing, Single Row, Version H, Polarized Friction Lock, 25 Circuits](#)

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-70058 \(PDF\)](#)
[Product Specification PS-70400 \(PDF\)](#)
[Product Specification PS-71851 \(PDF\)](#)
[Test Summary TS-70058-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [70066](#)
Application Signal, Wire-to-Board
Comments Version H
Overview [SL™ Modular Connectors](#)
Product Name SL™
UPC 800754609494

Physical

Circuits (maximum) 25
Color - Resin Black
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Polyester Alloy
Net Weight 2.228/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Stackable Yes
Temperature Range - Operating -40°C to +105°C

Electrical


Current - Maximum per Contact 3A

Material Info

Old Part Number 70066-0234

Reference - Drawing Numbers

Product Specification PS-70058, PS-70400, PS-71851
Sales Drawing SD-70066-0211-0234
Test Summary TS-70058-001



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[70066Series](#)

Mates With
[6373 Straight Header](#), [7478](#), [171856](#),
[171857](#)

Use With
SL™ Crimp Terminal [70058](#), [71851](#)