



| LOC | DIST | P | F | ZONE | LTR | REVISIONS                                 |           |      |
|-----|------|---|---|------|-----|-------------------------------------------|-----------|------|
|     |      |   |   |      |     | DESCRIPTION                               | DATE      | APPD |
| FT  | 13   |   |   |      | P   | REDRAWN & REVISED<br>PER ECN BD6668       | 08/26/92  | —    |
|     |      |   |   |      | R   | REV PER EC 0020-250-94                    | 03/24/94  | AT   |
|     |      |   |   |      | S   | OBSOLETE -2<br>PER EC 0020-596-96         | 09 JAN 97 | MM   |
|     |      |   |   |      | T   | REACTIVATED -2 &<br>REV PER EC 0G1C-25-98 | 11 MAR 98 | MM   |
|     |      |   |   |      | T1  | REVISED PER ECO-09-021826                 | 10SEP09   | AEG  |
|     |      |   |   |      |     |                                           |           |      |



PANEL CUTOUT

- PANEL RETENTION MECHANISM ACCOMMODATES PANEL THICKNESSES FROM 0.76[.030] TO 2.29[.090].
- SAME AS 207020-1 EXCEPT: ROUNDED EDGES ON THE OUTSIDE OF THE HOUSING AND A 45° ANGLE ON THE OUTSIDE OF THE HOUSING BY THE LOCKING LATCHES, REF 928097.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

|         |          |   |          |
|---------|----------|---|----------|
| 3       | OBSOLETE | 2 | 207020-2 |
|         |          |   | 207020-1 |
| PART NO |          |   |          |

|                                                                                                                                          |  |                                                                                                                                     |  |                                                        |  |
|------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------|--|
| DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON :<br>2 PLC DEC ± 0.25 [.010]<br>3 PLC DEC ± -<br>ANGLES ± - |  | DR 08/26/92<br>W.LENKER<br>CHK 8-31-92<br>R.STONE<br>APPD 9-2-92<br>A.TRAVIS<br>APPD 9-3-92<br>C.ROHDE<br>PRODUCT SPEC<br>108-10033 |  | AMP Incorporated<br>Harrisburg, PA 17105-3608          |  |
| MATERIAL<br>NYLON, COLOR: RED                                                                                                            |  | FINISH<br>-                                                                                                                         |  | NAME<br>HOUSING, RECEPTACLE,<br>36 POSITION, METRIMATE |  |
| APPLICATION SPEC<br>-                                                                                                                    |  | WEIGHT<br>-                                                                                                                         |  | SIZE<br>CAGE CODE<br>DRAWING NO<br>SCALE<br>2:1        |  |
|                                                                                                                                          |  |                                                                                                                                     |  | CAGE CODE<br>00779<br>C-207020                         |  |
|                                                                                                                                          |  |                                                                                                                                     |  | SHEET<br>1 OF 1                                        |  |

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.