

RH/Temperature Pen



Compact, Digital Hygro-Thermometer
Ideal for field use

Features:

- Dual LCD display for Temperature, Humidity, and advanced function indication
- Measures Temperature (°C/°F) and Relative Humidity simultaneously
- Built-in Temperature and Humidity sensors for convenient operation
- Max/Min memory functions for both Temperature & Relative Humidity
- Built-in self calibration utility with optional RH calibration bottles
- Data Hold for freezing the LCD display status
- Complete with pocket clip and 3V lithium battery
- Optional kit includes 33% and 75% RH Calibration Standards and hard vinyl carrying case



445582 RH Pen and Calibration Standards Kit



Specifications	% Relative Humidity	Temperature
Range	10 to 90%	14 to 122°F (-10 to 50°C)
Accuracy	±5%	±1.8°F/1°C
Resolution	0.1%RH	0.1°C or °F
Power	One lithium battery (CR2032)	
Dimensions	5.7x 1.2 x 1" (145 x 30 x 25mm)	
Weight	2.3 oz. (65g)	

Ordering Information:

445580RH/Temperature Pen
445580-NIST445580 with Calibration Traceable to NIST.
RH300-CAL33% and 75% RH calibration reference



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Extech:

[445582-NIST](#) [445580-NIST](#) [445582](#) [445580](#)