

Pan-Ty® NATURAL NYLON 6.6 CABLE TIES					
Part Number	Length (mm)	Width (mm)	Max. Bundle Dia. (mm)	Min. Loop Tensile Str. (N)	Std. Pkg. Qty.
Sub-Miniature					
PLT.6SM-C	71	1.8	15	36	100
Miniature					
PLT.7M-C	79	2.3	17	80	100
PLT1M-C	99	2.5	22	80	100
PLT1.5M-C	142	2.5	32	80	100
PLT2M-C	203	2.5	51	80	100
Intermediate					
PLT1.5I-C	142	3.6	35	178	100
PLT2I-C	203	3.6	51	178	100
PLT2.5I-C	246	3.7	64	178	100
PLT3I-C	290	3.7	76	178	100
PLT4I-C	368	3.7	102	178	100
Standard					
PLT1S-C	122	4.8	25	222	100
PLT1.5S-C	157	4.8	38	222	100
PLT2S-C	188	4.8	48	222	100
PLT2.5S-C	249	4.8	64	222	100
PLT3S-C	292	4.8	76	222	100
PLT4S-C	368	4.8	102	222	100
PLT4.5S-C	394	4.8	114	222	100
PLT5S-C	445	4.8	127	222	100
Light-Heavy					
PLT6LH-C	556	7.6	152	534	100
PLT7LH-C	627	7.6	178	534	100
PLT8LH-C	701	7.6	203	534	100
PLT9LH-C	775	7.6	229	534	100
PLT10LH-C	871	7.6	262	534	100
Heavy					
PLT2H-L	206	7.6	51	534	50
PLT2.5H-L	251	7.6	64	534	50
PLT3H-L	290	7.6	76	534	50
PLT4H-L	368	7.6	102	534	50
PLT5H-L	450	8.9	127	778	50
PLT6H-L	530	8.9	152	778	50



CPLTHEAD-B

PLT8H-L	779	8.9	229	778	50
PLT13H-Q	1100	8.9	330	778	25
Thousand Packs					
PLT1M-M	99	2.5	22	80	1,000
PLT1.5I-M	142	3.6	35	178	1,000
PLT2S-M	188	4.8	48	222	1,000
PLT4S-M	368	4.8	102	222	1,000

- One piece construction with multiple locking tooth design for consistent performance, greater strength and reliability
- High loop tensile strength exceeds industry standards
- UL Listed
- Lowest threading force of any one piece cable tie in the industry
- Bundle diameters up to 13" (330mm) or join together for larger diameters
- Miniature to standard cross sections feature a curved tip for easy threading and handling
- Finger tip grip assures positive grip & prevents tip from slipping out of head during threading

Pan-Ty® WEATHER RESISTANT NYLON 6.6 CABLE TIES

Part Number	Length (mm)	Width (mm)	Max. Bundle Dia. (mm)	Min. Loop Tensile Str. (N)	Std. Pkg. Qty.
Sub-Miniature					
PLT.6SM-C0	71	1.8	15	36	100
Miniature					
PLT1M-C0	99	2.5	22	80	100
PLT1.5M-C0	142	2.5	32	80	100
PLT2M-C0	203	2.5	51	80	100
Intermediate					
PLT1.5I-C0	142	3.6	35	178	100
PLT2I-C0	203	3.6	51	178	100
PLT2.5I-C0	246	3.7	64	178	100
PLT3I-C0	290	3.7	76	178	100
PLT4I-C0	368	3.7	102	178	100
Standard					
PLT1S-C0	122	4.8	25	222	100
PLT1.5S-C0	157	4.8	38	222	100
PLT2S-C0	188	4.8	48	222	100
PLT2.5S-C0	249	4.8	64	222	100
PLT3S-C0	292	4.8	76	222	100
PLT4S-C0	368	4.8	102	222	100
PLT4.5S-C0	394	4.8	114	222	100



CPLT-WR-B.jpg

PLT5S-C0	445	4.8	127	222	100
Light Heavy					
PLT6LH-C0	556	7.6	152	534	100
PLT7LH-C0	627	7.6	178	534	100
PLT8LH-C0	701	7.6	203	534	100
PLT9LH-C0	775	7.6	229	534	100
Heavy					
PLT2H-L0	206	7.6	51	534	50
PLT2.5H-L0	251	7.6	64	534	50
PLT3H-L0	290	7.6	76	534	50
PLT4H-L0	368	7.6	102	534	50
PLT5H-L0	450	8.9	127	778	50
PLT6H-L0	530	8.9	152	778	50
PLT8H-L0	779	8.9	229	778	50
PLT13H-Q0	1100	8.9	330	778	25
Thousand Packs					
PLT1M-M0	99	2.5	22	80	1,000
PLT1.5I-M0	142	3.6	35	178	1,000
PLT2S-M0	188	4.8	48	222	1,000
PLT4S-M0	368	4.8	102	222	1,000

- Weather Resistant Cable Ties, material resists ultraviolet light
- One piece construction with multiple locking tooth design for consistent performance, greater strength and reliability
- High loop tensile strength exceeds industry standards
- UL Listed
- Lowest threading force of any one piece cable tie in the industry
- Bundle diameters up to 13" (330mm) or join together for larger diameters
- Miniature to standard cross sections feature a curved tip for easy threading and handling
- Finger tip grip assure positive grip & prevents tip from slipping out of head during threading