

丸

形

Round Type


ϕ 4.0mm Series

Type No.	Lighting Color
LN29RPP	Red
LN29RCPP	Red
LN29WPP	Red
LN29CPP	Red

絶対最大定格 Absolute Maximum Ratings (Ta=25 °C)

Lighting Color	P _D (mW)	I _F (mA)	I _{FP} (mA)*	V _R (V)	T _{opr} (°C)	T _{stg} (°C)
Red	70	25	150	4	-25~+85	-30~+100

* I_{FP} の条件は, duty 10%, Pulse width 1 msec. The condition of I_{FP} is duty 10%, Pulse width 1 msec



電気的光学的特性 Electro-Optical Characteristics (Ta=25 °C)

Type No.	Lighting Color	Lens Color	I _O			V _F		λ_p	$\Delta \lambda$	I _F	I _R	
			Typ.	Min.	I _F	Typ.	Max.				Max.	V _R
LN29RPP	Red	Red Diffused	1.5	0.5	15	2.2	2.8	700	100	20	5	4
LN29RCPP	Red	Red Clear	3.5	1.5	15	2.2	2.8	700	100	20	5	4
LN29WPP	Red	White Diffused	1.5	0.5	15	2.2	2.8	700	100	20	5	4
LN29CPP	Red	Clear	5.0	1.9	15	2.2	2.8	700	100	20	5	4
Unit	—	—	mcd	mcd	mA	V	V	nm	nm	mA	μ A	V

