




AMP INCORPORATED

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

RECOMMENDED OPERATING TEMPERATURE:
105°C [221°F]

VOLTAGE RATING:
300V MAX

WIRE CROSS SECTIONAL AREA RANGE:
2.62-6.64mm² [5,180-13,100] CIR.MIL
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.127[.005]

4 PLC ± -

ANGLES ± 5°

FINISH

MATERIAL

5

6

DWN KIRAN HOLAL 03APR12

CHK ROHDE DANIEL 03APR12

APVD ROHDE DANIEL 03APR12

PRODUCT SPEC

APPLICATION SPEC

114-2156

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

WIRE TERMINAL

P.I.D.G SPADE

WIRE SIZE 12-10 AWG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=322985

SCALE 8:1

SHEET 1 OF 1

REV D3