


Compression Terminal 8

151-CJ9011-E

KOBI CONN

Compression Terminal 8

151-CJ9011-E



SPECIFICATIONS

Contact Resistance:	30m Ω max.
Insulation Resistance:	100M Ω min.
Wire Range:	14-20 AWG
Maximum Amount Rating:	DC50V4A
Minimum Retention Force:	50 N max.
Temperature Increase:	30°C max. (DC 4A)

RoHS Compliant

DIMENSIONS: mm (in.)

No.	Part Name	Material
1	Knob Handling	A.B.S. PA-757
2	Spring	SWAP
3	Insulation Set	A.B.S. PA-757
4	Terminal	C2680R-H t=0.6

Date Last Revised: 10-25-11

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC- 301062

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[151-CJ9011-E](#)