

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39537-7920

Status:

Active

Overview:

Eurostyle™ Terminal Blocks

Description:

5.08mm Pitch Eurostyle™ Horizontal Plug, with Retention Screws and Reverse Imprinting, Rear Wire Entry, Green Housing, Gold (Au) Plated, 20 Circuits

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

| General        |                                         |
|----------------|-----------------------------------------|
| Product Family | Terminal Blocks                         |
| Series         | 39537                                   |
| Application    | N/A                                     |
| Comments       | Rear Wire Entry with Reverse Imprinting |
| Component Type | Plug                                    |
| Overview       | Eurostyle™ Terminal Blocks              |
| Product Name   | ESE, Eurostyle™Pluggable                |
| Type           | Euro Block                              |
| UPC            | 822350676007                            |

| Physical                      |                                |
|-------------------------------|--------------------------------|
| Circuits (Loaded)             | 20                             |
| Entry Angle                   | Horizontal                     |
| Lock to Mating Part           | Yes                            |
| Number of Rows                | 1                              |
| Orientation                   | Vertical                       |
| Panel Mount                   | No                             |
| Pitch - Mating Interface      | 5.08mm                         |
| Pitch - Termination Interface | 5.08mm                         |
| Polarized to Mating Part      | Yes                            |
| Stackable                     | No                             |
| Temperature Range - Operating | -40°C to +105°C                |
| Wire Size AWG                 | 12, 14, 16, 18, 20, 22, 24, 26 |
| Wire Size mm²                 | 0.13 - 3.31                    |

| Electrical                    |      |
|-------------------------------|------|
| Current - Maximum per Contact | 18A  |
| Voltage - Maximum             | 300V |

Material Info

| Reference - Drawing Numbers |              |
|-----------------------------|--------------|
| Sales Drawing               | SD-39537-002 |



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

39537Series

Mates With

Most 5.08mm (.200") Pitch Industry Standard PCB Headers, 39535 Vertical PCB Header with Threaded Retention Inserts, 39536 Horizontal PCB Header with Threaded Retention Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39537-7920](#)