

**Terminal markers
ESO 14/6 DIN A4-BOGEN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The various connector markers from Weidmüller enable users to solve virtually every labelling task on all types of lines. Whether several lines of labelling, ready-to-use markers with standard printing, or individual labelling, whether white or coloured markers or common designations at the clamping points, the comprehensive range of products represent the easy, quick and clear answer to every marking task.

General ordering data

Order No.	1607740000
Type	ESO 14/6 DIN A4-BOGEN
Version	Terminal markers, 34 x 4 mm, Paper, Colour: White
GTIN (EAN)	4008190206130
Qty.	10 pc(s).

Terminal markers ESO 14/6 DIN A4-BOGEN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	34 mm	Width	4 mm
Height	1 mm	Net weight	12 g

Markings

Can be labelled with thermal transfer printers	No	Can be printed with plotter	Yes
Can be written with dot-matrix printer	No	Can be written with laser printer	Yes
Colour	White	Conductor O.D.	
Material	Paper	Material colour according to resistance code	9
Number per sheet	320	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Pin can be written (STI)	Yes
Pitch in mm (P)	6 mm	Speed marking laser	No

Classifications

ETIM 2.0	EC000761	ETIM 3.0	EC000761
UNSPSC	30-21-18-07	eClass 4.1	24-19-02-19
eClass 5.1	27-14-11-37	eClass 6.2	27-14-11-37
eClass 7.1	27-14-11-37		

Approvals

Approvals	
ROHS	Conform