



SMB/SMC Series

STRAIGHT BULKHEAD JACKS AND SOCKETS/50 OHM (for flexible cable)

**Crimp center contact
crimp outer
(male center contact)**




mounting detail




Cable Group ①	Body Plating	Contact Plating	Part Number	
			SMB	SMC
022	Gold	Gold	B65 H65 G022 X99	C65 H65 G022 X99
022	Bright Nickel	Gold	B65 H65 J022 X99	C65 H65 J022 X99
024	Gold	Gold	B65 H65 G024 X99	C65 H65 G024 X99
024	Bright Nickel	Gold	B65 H65 J024 X99	C65 H65 J024 X99

**Solder spill
rear mount socket
(male center contact)**




mounting detail




Body Plating	Contact Plating	Part Number	
		SMB	SMC
Gold	Gold	B65 M08 G999 X99	C65 M08 G999 X99
Bright Nickel	Gold	B65 M08 J999 X99	C65 M08 J999 X99

**Solder spill
front mount socket
(male center contact)**



mounting detail



Body Plating	Contact Plating	Part Number	
		SMB	SMC
Gold	Gold	B65 M18 G999 X99	C65 M18 G999 X99
Bright Nickel	Gold	B65 M18 J999 X99	C65 M18 J999 X99

① For cable group to cable type cross reference refer to page 200.
All diagrams are for SMB versions.
All dimensions are nominal.
For 75 ohm versions see page 157 to 167, or contact our sales office for uncataloged requirements.

All measurements are in millimeters unless otherwise specified.

M/A-COM, Inc.