

6-Outlet, Direct plug-in, 540 joules Surge Suppressor

MODEL NUMBER: **SK6-0**



Highlights

- 6 outlets/direct plug-in
- 540 joule rating
- \$10,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Applications

- Personal computers, CAD/CAM/CAE workstations, network nodes, file servers, point-of-sale terminals, audio/visual devices, and more.

Package Includes

- SK6-0 Surge Suppressor
- Warranty information
- Instruction manual

Description

The SK6-0 Surge Suppressor from Tripp Lite is ideal for protecting audio/video devices and printers. This direct plug-in surge suppressor features 6 outlets and 540 joules of surge energy absorption. \$10,000 Ultimate Lifetime Insurance (USA & Canada only).

Features

- 6 outlets; direct plug-in
- Surge energy absorption: 540 joules; 27,000 amps
- \$10,000 Ultimate Lifetime Insurance (USA and Canada Only)

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	6 NEMA 5-15R
Transformer accommodation	Holds up to 4 large transformer plugs
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P input plug
Input cord length details	Direct Plug-In
Voltage compatibility (VAC)	120
Maximum Surge Amps	36000
UPC ASSIGNMENT	
Unit Carton UPC#	037332010261
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	540
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150V
AC suppression surge current rating	27,000 amps
UL1449 let through rating	400, 500, 500
Immunity	Conforms to IEE 587 / ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (HWD/in)	1.18 x 4.53 x 4.75
Shipping Dimensions (HWD/cm)	3 x 11.5 x 12
Shipping weight (lbs)	.55
Shipping weight (kg)	.25
Unit Dimensions (HWD/in)	4.80 x 4.35 x 1.42
Unit Dimensions (HWD/cm)	12.19 x 11.05 x 3.6
Unit weight (lbs)	.406
Unit weight (kg)	.18
Material of construction	Plastic
Integrated keyhole mounting tabs	Direct plug-in suppressor mounts directly to a wall receptacle
Housing Color	Light Gray
Receptacle Color	Light Gray



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Style	Direct plug-in
Outlets center to center measurement	Distance between horizontal outlets = 25.2mm; Distance between vertical outlets = 39mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[S8+TEL](#)