

Audio Connector, Plug, 2.5 mm, 2-pole, solder terminal, insulated, angled



Description

- Solder terminal:
for cable mounting
- Audio entrances and exits
- Data and Signal transfer
- Audio Plug: 2-pole, insulated, angled

References

Alternative: Housing shielded 4831.1200

Weblinks


pdf-datasheet, html-datasheet, General Product Information, RoHS, CHINA-RoHS, REACH, Mating Connectors, e-Shop, SCHURTER-Stock-Check, Distributor-Stock-Check

Technical Data

Diameter	2.5 mm
Number of Poles	2-pole
Ratings DC	0.5 A / 30 VDC
Ratings AC	0.5 A / 30 VAC
Dielectric Strength	500 VDC
Insulation Resistance	> 100 MΩ @ 500 VDC

Allowable Operation Temp.	-20 °C to 70 °C
Terminal	solder terminal nickel-plated
Housing	insulated
Style	angled
Lifetime	5000 Insertions

Dimensions



Cable diameter max. 4.0 mm

All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Audio Plug/Sockets	2.5	2-pole	solder terminal	4831.1220

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 100 Pcs

Mating Outlets/Connectors

Category / Description



[Audio Plug/Sockets Overview complete](#)

4831, solder terminal, screened, 2-pole, Audio Plug/Sockets, 2.5 mm	4831.2200
4831, PCB terminals, screened, 2-pole, Audio Plug/Sockets, 2.5 mm	4831.2220
4831, PCB terminals, insulated, 2-pole, Audio Plug/Sockets, 2.5 mm	4831.2230
4831, solder terminal, insulated, 2-pole, Audio Plug/Sockets, 2.5 mm	4831.3200

[Audio Plug/Sockets further types to 4831 Audio-Stecker, D=2,5mm](#)