

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF-Fiber Optic ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips [?](#)

☒ Text Search: 'F94D5-5M5Y'

Your search criteria matched only one product, shown below

F94D5-5M5Y



- Pass all TIA/EIA-568-B.3 performance requirements
 - FOCIS-5 compliant
 - 100% factory inspected end face geometry (SC, ST, and FJ® end faces are 100% inspected in compliance with Telcordia GR-326-CORE, Issue 3)
 - Insertion loss per mated pair: 0.50dB typical; 0.75dB max.
 - 8-degree APC polish (55dB minimum Return Loss) on singlemode MTP* and UPC polish (55dB minimum Return Loss) on singlemode SC and ST satisfy high-speed network application requirements
 - Factory terminated and 100% tested for insertion loss and return loss
 - Insertion loss and return loss data recorded for every singlemode cable assembly
 - Lifetime traceability of test data to a Q.C. number on each cable assembly
- *MTP is a registered trademark of US Conec Ltd.

▪ Part Number	F94D5-5M5Y
▪ RoHS Compliancy Status	Compliant
▪ Note	F94D5-5M5Y replaces F94D5-5M5
▪ Part Description	Female MTP* to female MTP* 4-fiber interconnect cable assembly (one female MTP* connector on each end on ribbon interconnect cable) – 9/125µm. Outside diameter: 5mm x 2.5mm.
▪ Product Type	MTP* Interconnect Cable Assemblies
▪ Length (m)	5
▪ Fiber Compatibility	9/125µm
▪ Fiber Type	Singlemode
▪ Cable Color	Yellow
▪ Cable Type	Duplex
▪ CE Compliant	No
▪ Connector 1 Type	MTP* Connector
▪ Connector 2 Type	MTP* Connector
▪ End Configurations	MTP* to MTP*
▪ Fiber Count	4
▪ Pricing Description	PC 4-Fiber Singlemode MTP*-MTP* 9µm 5m
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.