




- 1 HOUSING: NYLON, FLAME RETARDANT, UL 94V-O RATED, GLASS FILLED, BLACK.
- 2 CONTACTS AND GROUND CONTACT: 2.54 μm [.000100] MIN TIN OVER 1.27 μm [.000050] MIN NICKEL.
3. MATING FACE CONFORMS TO DIN SPECIFICATION 41524.
- 4 CONTACTS AND GROUND CONTACT: BRASS.

TUBE	5211450-2
GANG OF TUBES	5211450-1
PACKAGING TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11-11-04 L. VARELA - DOCK5 CHK 11-11-04 C. ROHDE		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± 0° 30'		NAME APVD 11-11-04 M. WALMSLEY PRODUCT SPEC 108-10047 APPLICATION SPEC 114-40025	
		MATERIAL 		RECEPTACLE ASSEMBLY, 5 POSN, RIGHT ANGLE, CIRCULAR DIN -	
FINISH 		WEIGHT -		SIZE A2	
		CAGE CODE 00779		DRAWING NO C-5211450	
		RESTRICTED TO -			
CUSTOMER DRAWING				SCALE	4:1
				SHEET	1 of 1
				REV	P