




Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	3/0 STR/FLEX
Wire Type	Stranded Copper: Class B & C Compact, Class G, H, I, K, M, Locomotive
Wire Strip Length	1-5/8 in.
Stud Size	1/4 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	ORANGE
Panduit Die Index No. on Barrel	P50
Alternate Industry Die Index No. () on Barrel	(14)



LISTED
Wire Connector



						<div><div>PANDUIT</div><div>CORP. TINLEY PARK, ILLINOIS</div></div>
						LCCX3/0-14BF-X Copper Lug - Two-Hole, Long Flex Barrel with Window, 90° Angle Tongue
00	6/03	SAC	SAC	RELEASED	10850	
REV	DATE	BY	CHK	DESCRIPTION	ECN	<div>SCALE N/A</div> <div>DRAWING NO / CAD FILE LCCX3_0-14BF-CUST</div>