

Connection Units

Chrome and Satin Chrome



Description

This uniquely shaped range is easy to install, with coloured terminals, clear white terminal markings and is supplied in individual display boxes.

Features

- black or white inserts available
- matching metal rocker versions
- lockable fuse carrier for safety isolation
- captive fuse barrier
- clear white terminal markings
- colour coded terminals
- discreet neon versions
- neon leads enclosed
- 2 earth terminals
- captive and backed out terminals
- terminals have large lead-ins
- 25 year guarantee

Range

plastic switch rockers

unswitched	1910
unswitched with flex outlet	1911
switched DP	1913
switched DP with neon	1914
switched DP with flex outlet	1915
switched DP with neon and flex outlet	1916

metal capped switch rockers

switched DP	2913
switched DP with neon	2914
switched DP with flex outlet	2915
switched DP with neon, flex outlet	2916

Prefix with finish

chrome	CH
satin chrome	SC
white or black inserts	W or B

Technical Specification

voltage rating	250Vac
current Rating	13A
contact gap	3m m

no user serviceable parts, except BS 1362 fuse links

Back Boxes

minimum recommended depth

	Flush 25m m	Dry lining 35m m
1g	DB162	DB2540

Standards

- BS 1363 Part 4 as applicable

Terminal Capacity

	2.5m m ²	4m m ²	6m m ²	10m m ²
L & N	4	3	2	1

DETA

Kingsway House, Laporte Way
Luton, Beds LU4 8RJ

Tel. +44 1582 544 500 Fax: +44 1582 544 501
Technical Helpline +44 1582 544 548