


PART NAME	NEMA 4X DIE CAST ALUMINUM ENCLOSURE	PART No.	AN-1310, AN-1310-G, AN-2810 & AN-2810-B	REV. DATE	12-17-08
-----------	-------------------------------------	----------	---	-----------	----------




MATERIAL: ALUMINUM ALLOY #ADC-12


FINISH: NATURAL (NO SUFFIX)
GRAY (SUFFIX -G)
SMOOTH BLACK (SUFFIX -B)

NOTES:



- 1) FOUR (4) M4 x 32mm (1.260") LG. SCREWS SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
- 2) ALL HOLE DIAMETERS HAVE ± 0.005 TOLERANCE
ALL OTHER DIMENSIONS HAVE ± 0.015 TOLERANCE




DETAIL 'D'



M4 x 0.7mm THREAD
(4) PLACES



SECTION 'A-A'



COVER

SEE DETAIL 'D'
SECTION 'C-C'

BODY

SECTION 'B-B'

PART NO. AN-2810 & AN-2810-B
ARE SUPPLIED WITH A WELDED
ON MOUNTING BRACKET ONLY.