

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Precision wire strippers
Catalogue number	3757
Date	03/04/2007

Range Description

A range of precision wire strippers

Features

- Compact design – convenient to carry
- Precision wire stripping – damage free wire preparation every time
- Depth stop adjustable up to 50mm with 1mm graduations – accurate and repeatable wire stripping
- Specially hardened blades – for a long life
- ESD version available for ESD safe areas



3756



3755



3757ESD



3757

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3756 20	Precision wire stripper for 0.2mm Diameter Wire	5013969497809	82032090	1
T3756 25	Precision wire stripper for 0.25mm Diameter Wire	5013969497908	82032090	1
T3756 30	Precision wire stripper for 0.3mm Diameter Wire	5013969498004	82032090	1
T3756 40	Precision wire stripper for 0.4mm Diameter Wire	5013969498103	82032090	1
T3756 50	Precision wire stripper for 0.5mm Diameter Wire	5013969498202	82032090	1
T3756 60	Precision wire stripper for 0.6mm Diameter Wire	5013969498301	82032090	1
T3756 80	Precision wire stripper for 0.8mm Diameter Wire	5013969498400	82032090	1
T3756 100	Precision wire stripper for 1.0mm Diameter Wire	5013969497700	82032090	1
T3757ESD 2	Precision wire stripper for 0.25 to 0.8mm Diameter Wire	5013969020434	82032090	1
T3755 018	Precision Fibre optic wire stripper for 0.18mm Diameter Cable	5013969489507	82032090	1
330009	Precision wire stripper 0.12 to 0.4mm Diameter Wire	5051073300097	82032090	1
330011	Precision wire stripper 0.3 to 1.0mm Diameter Wire	5051073300110	82032090	1
330013	Precision wire stripper for 0.25 to 0.8mm Diameter Wire	5051073300103	82032090	1

Technical product information	Wire types									
	For PVC, Teflon and similar coated wires									
	Wire stripping capacities									
	<table><tr><td rowspan="2">T3756 20</td><td>mm</td><td>0.2</td></tr><tr><td>awg</td><td>32</td></tr><tr><td>T3756 25</td><td>mm</td><td>0.25</td></tr></table>			T3756 20	mm	0.2	awg	32	T3756 25	mm
T3756 20	mm	0.2								
	awg	32								
T3756 25	mm	0.25								

	T3756 30	awg	30					
		mm	0.3					
	T3756 40	awg	28					
		mm	0.4					
	T3756 50	awg	26					
		mm	0.5					
	T3756 60	awg	24					
		mm	0.6					
	T3756 80	awg	22					
		mm	0.8					
	T3756 100	awg	20					
		mm	1					
	T3757ESD 2	awg	18					
		mm	0.25	0.3	0.4	0.5	0.6	0.8
	330009	awg	30	28	26	24	22	20
		mm	0.12	0.16	0.2	0.25	0.3	0.4
	330011	awg	36	34	32	30	28	26
		mm	0.3	0.4	0.5	0.6	0.8	1
	330013	awg	28	26	24	22	20	18
		mm	0.25	0.3	0.4	0.5	0.6	0.8
Standards compliance	None applicable							
User health and safety information	None applicable							
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations							
Material safety data	None applicable							
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered							
Country of origin	Germany							

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3756 20	98	10	54	24	98	10	54	25
T3756 25	98	10	54	24	98	10	54	25
T3756 30	98	10	54	24	98	10	54	25
T3756 40	98	10	54	24	98	10	54	25
T3756 50	98	10	54	24	98	10	54	25
T3756 60	98	10	54	24	98	10	54	25
T3756 80	98	10	54	24	98	10	54	25

T3756 100	98	10	54	24	98	10	54	25
T3757ESD 2	98	10	54	26	98	10	54	27
T3755 018	98	10	54	26	98	10	54	27
330009	98	10	54	26	98	10	54	27
330011	98	10	54	26	98	10	54	27
330013	98	10	54	26	98	10	54	27

Shelf box (secondary packaging)					Euro Pallet data Wi x Hi	
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3756 20	-	-	-	-		
T3756 25	-	-	-	-		
T3756 30	-	-	-	-		
T3756 40	-	-	-	-		
T3756 50	-	-	-	-		
T3756 60	-	-	-	-		
T3756 80	-	-	-	-		
T3756 100	-	-	-	-		
T3757ESD 2	-	-	-	-		
T3755 018	-	-	-	-		
330009	-	-	-	-		
330011	-	-	-	-		
330013	-	-	-	-		

Packaging waste details

Primary Packaging					Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3756 20	1	Bag						
T3756 25	1	Bag						
T3756 30	1	Bag						
T3756 40	1	Bag						
T3756 50	1	Bag						
T3756 60	1	Bag						
T3756 80	1	Bag						
T3756 100	1	Bag						
T3757ESD 2	1	Bag						

T3755 018	1	Bag						
330009	1	Bag						
330011	1	Bag						
330013	1	Bag						