



SIZE	Part Num.	Threading	Jackscrew colour
25	86303639BLF	UNC 4.40	black
	86303644BLF	M3	grey
	86303644B100LF	M3	grey

See table for
colour coding



NOTES:

Material: Nylon (UL94V-2)

Cable strain relief: Cable clamp with
Self-taping screws

Temperature range: -40°C to 95°C

Cable diameter: 4.0 to 11.0mm

Jackscrew colour: black for 4.40 UNC}
grey for M3.0

Packaging: - Part Num. ending BLF = Box of 100
individual sets.
- Part Num. ending B100LF = Box of bulk
components in plastic bags (see
quantity on the table).

Cable clamp screwing force (max): 70 Ncm


Jack screws screwing force (max): 50 Ncm

- The "LF" product meets European Union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- packaging spec; see GS-14-920.

DESIGNATION	REP	Qty per set	Qty per bulk
BACKSHELL	1	1	100
JACKSCREWS	2	2	200
GROMMET	3	1	100
CABLECLAMP	4	1	100
SCREWS POZIDRIVE	5	2	200

rev	ecn no	dr	date
A	LS05-0086	LGO	2005/10/10
B	LS06-0084	LGO	2006/06/20
C	LS08-0155	MPE	2008/06/27
D	F09-0223	LSA	2009/11/24
E	F10-0083	LSA	2010/08/04
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		- ✓	tolerance std ISO 406 ISO 1101		projection 		 mm		
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	GOISNARD L	2004.03.22	ANGULAR	LINEAR	0.X		±/	size A3	Scale 3:2			
Eng	PESSON M	2004.03.22			0.XX		±/					
Chr	LEGARE .P	2004.03.22			0°	±°	0.XXX					±/
Appr	LEGARE P	2004.03.22	Product family					D-SUB HOODS		Spec ref		
			title					dwg no		Rev		
			D-SUB PLASTIC SHELLS					10061215C		E		
			STRAIGHT SNAP-TOGETHER									
			catalog no			see tables		CUSTOMER		sheet 1 of 3		



SIZE	Part Num.	Threading	Jackscrew colour	Packaging box
9	86303637BLF	UNC 4.40	Black	Individual sets
	86553329BLF	M3	Grey	Individual sets
	86553329B100LF	M3	Grey	Individual bulks

SIZE	Part Num.	Threading	Jackscrew colour	Packaging box
15	86303638BLF	UNC 4.40	Black	Individual sets
	86553330BLF	M3	Grey	Individual sets
	86553330B100LF	M3	Grey	Individual bulks


SIZE	Part Num.	Threading	Jackscrew colour
37	86303640BLF	UNC 4.40	black
	86303645BLF	M3	grey
	86303645B100LF	M3	grey

www.fciconnect.com			surface ISO 1302		- 		tolerance std ISO 406 ISO 1101		projection 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	GOISNARD L	2004.03.22	ANGULAR	LINEAR	0.X		±/		size A3	Scale 1:1		
Eng	PESSON M	2004.03.22			0.XX		±/					
Chr	LEGARE.P	2004.03.22			0.XXX		±/					
Appr	LEGARE P	2004.03.22	0° ±°		ECN				F10-0083			
Product family			D-SUB HOODS				Spec ref		-			
			D-SUB PLASTIC SHELLS STRAIGHT SNAP-TOGETHER				dwg no 10061215C		Rev. E			
			catalog no		see tables		CUSTOMER		sheet 2 of 3			


REV C - 2006-03-28

CABLING INSTRUCTIONS


1- Choose grommet position




2- Mount connector and cable inside



3- Mount cableclamp and screws



4- Close the backshell and click together



Copyright FCI.

www.fciconnect.com			surface ISO 1302		- ✓ tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	GOISNARD L	2004.03.22	ANGULAR 0° ±°	LINEAR	0.X ±/		size A3	Scale 1:1		
Eng	PESSON M	2004.03.22			0.XX ±/					
Chr	LEGARE .P	2004.03.22			0.XXX ±/					
Appr	LEGARE P	2004.03.22	Product family D-SUB HOODS				Spec ref			
	title D-SUB PLASTIC SHELLS STRAIGHT SNAP-TOGETHER				dwg no 10061215C		Rev E			
	catalog no		see tables		CUSTOMER		sheet 3 of 3			

REV E - 2006-03-28

PDM: Rev:E

STATUS Released

Printed: Oct 01, 2010